

Conductor Type	Conductor Range	Wire Diameter (in.)
Concentric, compressed, and compact copper stranding	650 MCM	.930

Stud Size	1/2"
No. of Holes in Pad	2 (1 3/4" centers)

Additional Details

UL Listing	CU 90°C / UL486A Power
CSA Listing	CSA C22.2 No. 65 Power

Approximate Dimensions

B (in.)	2 13/32
D (in.)	3.00
E (in.)	1 3/4
L (in.)	6.68
T (in.)	.27
W (in.)	1.78

Installation Tools & Dies

Die Color Code	Pink
TDY-1 Pressure Setting	9
TDY-U Pressure Setting	9
Burndy Die Index	B-300
Huskie / PUC Die Set	HT41FB
T & B Die	99H or 99