



Representative

**Catalog Number:** ASP500  
**Product ID:** 7TAH007890R1143  
**UPC Number:** 78378661073  
**Status:** Active

Type ASP Aluminum Splice, Max 35KV, Wire Size 500 kcmil, Length 5 Inch, Tin Plated, Die Color Code Pink

- Made of high-conductivity seamless aluminum tubing. Tin plated for corrosion resistance.
- Specifically chamfered barrel for ease of installation.
- Color-coded for matching die identification. Prefilled with oxide inhibiting compound.

### North American Specifications (UNSPSC)

UNSPSC	39121449 Wire or cable compression splice
IGCC	4669 Wire or cable compression splice
Brand Name	Blackburn
Type	Aluminum Splice
Special Features	Made of high-conductivity seamless aluminum tubing. Tin plated for corrosion resistance.
Standard	UL E9809
Material	Aluminum
Finish	Tin Plated
Color	Pink
Voltage Rating	35KV

### Packaging

Inner Quantity	2
Inner Dimensions (inches)	5.3x3.9x2.7
Outer Quantity	20
Outer Dimensions (inches)	15.1x8.1x6.1
Weight Uom	43 lbs. per 100

### Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)