



Actual

Catalog Number: CSR 250
Product ID: 7TAH006410R0058
UPC Number: 78378671531
Status: Active

Aluminum Multi-Tap Encapsulated Splice One-Way Configuration, 2 Outlets, Wire Range 250 kcmil-6 Str, Length 4.0 Inches, Width 1.06 Inches, Height 2.0 Inches, Hex Size 5/16 Inch, Clear Insulation

North American Specifications (UNSPSC)

UNSPSC	39121408 Mechanical connectors
IGCC	4541 Mechanical connectors
Brand Name	Homac
Type	Multi-Tap Encapsulated Splice
Special Features	Versatile design. Wide range of cable sizes and number of outlets available in one-way configurations.
Standard	UL E9809
Material	Aluminum
Color	Clear
Voltage Rating	600V
Insulation	PVC
Number Of Ports	2

Packaging

Outer Quantity	10
Outer Dimensions (inches)	7.5x6.8x4.7
Weight Uom	21.5 lbs. per 100

Documents / Support Tools

SDS US 1	sds-00041-tb2
Technical Data Sheet Global	wsd-000518
Marketing Brochure US 1	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com