

28 Series 28.50 x 17.00 x 11.33 (724 x 432 x 288) Replacement Filter No. 10100056

Catalog Number	Voltage	Hz	Phase	BTU/Hr @ 125°F/125°F	Full Load Amps	Max. Ambient Temp., °F/°C	Shipping Weight Lbs./Kgs
M280216G013	115	50/60	1	2200/2200	9.8/9.0	125/52	98/45
M280226G004	230	50/60	1	2200/2200	5.0/4.5	125/52	98/45
M280246G400	460	50/60	1	2200/2200	2.8/2.5	125/52	108/49
M280416G007	115	50/60	1	3800/4000	14.6/14.0	125/52	116/53
M280426G032	230	50/60	1	3800/4000	7.4/6.9	125/52	116/53
M280446G400	460	50/60	1	3800/4000	4.1/3.8	125/52	136/62

33NSM Series 34.37 x 12.00 x 9.88 (873 x 305 x 251) Replacement Filter No. 10100057

Catalog Number	Voltage	Hz	Phase	BTU/Hr @ 125°F/125°F	Full Load Amps	Max. Ambient Temp., °F/°C	Shipping Weight Lbs./Kgs
M330416G010	115	50/60	1	3700/4000	13.0/13.2	125/52	105/48
M330426G009	230	50/60	1	3700/4000	7.2/7.3	125/52	105/48
M330446G400	460	50/60	1	3700/4000	4.0/4.0	125/52	125/57

36N Series 38.72 x 15.00 x 11.33 (984 x 381 x 288) Replacement Filter No. 10100056

Catalog Number	Voltage	Hz	Phase	BTU/Hr @ 125°F/125°F	Full Load Amps	Max. Ambient Temp., °F/°C	Shipping Weight Lbs./Kgs
M360616307	115	50/60	1	5000/6000	14.0/14.0	125/52	120/54
M360626306	230	50/60	1	5000/6000	7.0/7.0	125/52	120/54
M360646400	460	50/60	1	5000/6000	3.9/3.9	125/52	140/64