

## Air Conditioners

Catalog Number	AxBxC in./mm	Model Style	Rated Voltage	Frequency (Hz)	Phase	BTUs/Hr. at	BTUs/Hr. at	Full Load Amps at 50/60 Hz	Max. Amb. Temp. (°F/°C)	Min. Amb. Temp. (°F/°C)	Starting Current (Amps)	Wt. (lb./kg)
						131 F/131 F (55 C/55 C)	95 F/95 F (35 C/35 C)					
<b>G280446G051</b>	28.55 x 16.97 x 10.10 725 x 431 x 257	Indoor Stainless Steel Type 4X	460	50/60	3~	4600/4900	4324/4655	1.3/1.4	131/55	-40/-40	7.7	84/38
<b>G280446G100</b>	28.55 x 16.97 x 10.10 725 x 431 x 257	Outdoor without Heat Pkg.	460	50/60	3~	4600/4900	4324/4655	1.3/1.4	131/55	-40/-40	7.7	84/38
<b>G280616G050</b>	28.55 x 16.97 x 10.10 725 x 431 x 257	Indoor	115	50/60	3~	4600/4900	4324/4655	1.3/1.4	131/55	-40/-40	7.7	84/38
<b>G280616G051</b>	28.55 x 16.97 x 10.10 725 x 431 x 257	Indoor Stainless Steel Type 4X	115	50/60	1	6000/6400	5600/6000	9.9/11.4	131/55	-40/-40	36.2	84/38
<b>G280616G100</b>	28.55 x 16.97 x 10.10 725 x 431 x 257	Outdoor without Heat Pkg.	115	50/60	1	6000/6400	5600/6000	9.9/11.4	131/55	-40/-40	36.2	84/38
<b>G280616G150</b>	28.55 x 16.97 x 10.10 725 x 431 x 257	Outdoor with Heat Pkg.	115	50/60	1	6000/6400	5600/6000	9.9/11.4	131/55	-40/-40	36.2	84/38
<b>G280626G050</b>	28.55 x 16.97 x 10.10 725 x 431 x 257	Indoor	230	50/60	1	6000/6400	5600/6000	9.9/11.4	131/55	-40/-40	36.2	84/38
<b>G280626G051</b>	28.55 x 16.97 x 10.10 725 x 431 x 257	Indoor Stainless Steel Type 4X	230	50/60	1	6000/6400	5600/6000	4.6/5.8	131/55	-40/-40	17.7	84/38
<b>G280626G100</b>	28.55 x 16.97 x 10.10 725 x 431 x 257	Outdoor without Heat Pkg.	230	50/60	1	6000/6400	5600/6000	4.6/5.8	131/55	-40/-40	17.7	84/38
<b>G280626G150</b>	28.55 x 16.97 x 10.10 725 x 431 x 257	Outdoor with Heat Pkg.	230	50/60	1	6000/6400	5600/6000	4.6/5.8	131/55	-40/-40	17.7	84/38
<b>G280646G050</b>	28.55 x 16.97 x 10.10 725 x 431 x 257	Indoor	460	50/60	1	6000/6400	5600/6000	4.6/5.8	131/55	-40/-40	17.7	84/38
<b>G280646G051</b>	28.55 x 16.97 x 10.10 725 x 431 x 257	Indoor Stainless Steel Type 4X	460	50/60	3~	5400/6000	5054/5685	1.3/1.4	131/55	-40/-40	7.7	84/38
<b>G280646G100</b>	28.55 x 16.97 x 10.10 725 x 431 x 257	Outdoor without Heat Pkg.	460	50/60	3~	5400/6000	5054/5685	1.3/1.4	131/55	-40/-40	7.7	84/38

Indoor Cutout Adapter, part number 28621601, enables SPECTRACOOL to be mounted to a GENESIS M28 Air Conditioner cutout.

Outdoor Cutout Adapter, part number 28621603, enables SPECTRACOOL to be mounted to a T-Series T29 Air Conditioner cutout.

460 V, 3-phase units use R134a refrigerant