

| Catalog Number | AxBxC in.            | AxBxC mm        | Style      | Number of Cover Screws |
|----------------|----------------------|-----------------|------------|------------------------|
| ASE12X8X4NK    | 12.00 x 8.00 x 4.00  | 305 x 203 x 102 | Painted    | 4                      |
| ASG12X8X4NK    | 12.00 x 8.00 x 4.00  | 305 x 203 x 102 | Galvanized | 4                      |
| ASE12X10X4NK   | 12.00 x 10.00 x 4.00 | 305 x 254 x 102 | Painted    | 4                      |
| ASG12X10X4NK   | 12.00 x 10.00 x 4.00 | 305 x 254 x 102 | Galvanized | 4                      |
| ASE12X12X4NK   | 12.00 x 12.00 x 4.00 | 305 x 305 x 102 | Painted    | 4                      |
| ASG12X12X4NK   | 12.00 x 12.00 x 4.00 | 305 x 305 x 102 | Galvanized | 4                      |
| ASE15X15X4NK   | 15.00 x 15.00 x 4.00 | 381 x 381 x 102 | Painted    | 4                      |
| ASG15X15X4NK   | 15.00 x 15.00 x 4.00 | 381 x 381 x 102 | Galvanized | 4                      |
| ASE16X12X4NK   | 16.00 x 12.00 x 4.00 | 406 x 305 x 102 | Painted    | 4                      |
| ASG16X12X4NK   | 16.00 x 12.00 x 4.00 | 406 x 305 x 102 | Galvanized | 4                      |
| ASE18X12X4NK   | 18.00 x 12.00 x 4.00 | 457 x 305 x 102 | Painted    | 4                      |
| ASG18X12X4NK   | 18.00 x 12.00 x 4.00 | 457 x 305 x 102 | Galvanized | 4                      |
| ASE18X15X4NK   | 18.00 x 15.00 x 4.00 | 457 x 381 x 102 | Painted    | 4                      |
| ASE18X18X4NK   | 18.00 x 18.00 x 4.00 | 457 x 457 x 102 | Painted    | 4                      |
| ASG18X18X4NK   | 18.00 x 18.00 x 4.00 | 457 x 457 x 102 | Galvanized | 4                      |
| ASE24X12X4NK   | 24.00 x 12.00 x 4.00 | 610 x 305 x 102 | Painted    | 4                      |
| ASE24X18X4NK   | 24.00 x 18.00 x 4.00 | 610 x 457 x 102 | Painted    | 4                      |
| ASG24X18X4NK   | 24.00 x 18.00 x 4.00 | 610 x 457 x 102 | Galvanized | 4                      |
| ASE24X24X4NK   | 24.00 x 24.00 x 4.00 | 610 x 610 x 102 | Painted    | 4                      |
| ASG24X24X4NK   | 24.00 x 24.00 x 4.00 | 610 x 610 x 102 | Galvanized | 4                      |
| ASE30X24X4NK   | 30.00 x 24.00 x 4.00 | 762 x 610 x 102 | Painted    | 6                      |
| ASE30X30X4NK   | 30.00 x 30.00 x 4.00 | 762 x 762 x 102 | Painted    | 8                      |
| ASE6X6X6NK     | 6.00 x 6.00 x 6.00   | 152 x 152 x 152 | Painted    | 2                      |
| ASG6X6X6NK     | 6.00 x 6.00 x 6.00   | 152 x 152 x 152 | Galvanized | 2                      |
| ASE8X6X6NK     | 8.00 x 6.00 x 6.00   | 203 x 152 x 152 | Painted    | 2                      |
| ASG8X6X6NK     | 8.00 x 6.00 x 6.00   | 203 x 152 x 152 | Galvanized | 2                      |
| ASE8X8X6NK     | 8.00 x 8.00 x 6.00   | 203 x 203 x 152 | Painted    | 4                      |
| ASG8X8X6NK     | 8.00 x 8.00 x 6.00   | 203 x 203 x 152 | Galvanized | 4                      |
| ASE10X8X6NK    | 10.00 x 8.00 x 6.00  | 254 x 203 x 152 | Painted    | 4                      |
| ASG10X8X6NK    | 10.00 x 8.00 x 6.00  | 254 x 203 x 152 | Galvanized | 4                      |
| ASE10X10X6NK   | 10.00 x 10.00 x 6.00 | 254 x 254 x 152 | Painted    | 4                      |
| ASG10X10X6NK   | 10.00 x 10.00 x 6.00 | 254 x 254 x 152 | Galvanized | 4                      |
| ASE12X6X6NK    | 12.00 x 6.00 x 6.00  | 305 x 152 x 152 | Painted    | 4                      |
| ASE12X8X6NK    | 12.00 x 8.00 x 6.00  | 305 x 203 x 152 | Painted    | 4                      |
| ASG12X8X6NK    | 12.00 x 8.00 x 6.00  | 305 x 203 x 152 | Galvanized | 4                      |
| ASE12X10X6NK   | 12.00 x 10.00 x 6.00 | 305 x 254 x 152 | Painted    | 4                      |
| ASG12X10X6NK   | 12.00 x 10.00 x 6.00 | 305 x 254 x 152 | Galvanized | 4                      |
| ASE12X12X6NK   | 12.00 x 12.00 x 6.00 | 305 x 305 x 152 | Painted    | 4                      |
| ASG12X12X6NK   | 12.00 x 12.00 x 6.00 | 305 x 305 x 152 | Galvanized | 4                      |
| ASE16X12X6NK   | 16.00 x 12.00 x 6.00 | 406 x 305 x 152 | Painted    | 4                      |
| ASG16X12X6NK   | 16.00 x 12.00 x 6.00 | 406 x 305 x 152 | Galvanized | 4                      |
| ASE16X16X6NK   | 16.00 x 16.00 x 6.00 | 406 x 406 x 152 | Painted    | 4                      |
| ASG16X16X6NK   | 16.00 x 16.00 x 6.00 | 406 x 406 x 152 | Galvanized | 4                      |
| ASE18X12X6NK   | 18.00 x 12.00 x 6.00 | 457 x 305 x 152 | Painted    | 4                      |
| ASG18X12X6NK   | 18.00 x 12.00 x 6.00 | 457 x 305 x 152 | Galvanized | 4                      |
| ASE18X18X6NK   | 18.00 x 18.00 x 6.00 | 457 x 457 x 152 | Painted    | 4                      |
| ASG18X18X6NK   | 18.00 x 18.00 x 6.00 | 457 x 457 x 152 | Galvanized | 4                      |
| ASE24X12X6NK   | 24.00 x 12.00 x 6.00 | 610 x 305 x 152 | Painted    | 4                      |
| ASG24X12X6NK   | 24.00 x 12.00 x 6.00 | 610 x 305 x 152 | Galvanized | 4                      |
| ASE24X18X6NK   | 24.00 x 18.00 x 6.00 | 610 x 457 x 152 | Painted    | 4                      |
| ASG24X18X6NK   | 24.00 x 18.00 x 6.00 | 610 x 457 x 152 | Galvanized | 4                      |
| ASE24X20X6NK   | 24.00 x 20.00 x 6.00 | 610 x 508 x 152 | Painted    | 4                      |
| ASG24X20X6NK   | 24.00 x 20.00 x 6.00 | 610 x 508 x 152 | Galvanized | 4                      |
| ASE24X24X6NK   | 24.00 x 24.00 x 6.00 | 610 x 610 x 152 | Painted    | 4                      |
| ASG24X24X6NK   | 24.00 x 24.00 x 6.00 | 610 x 610 x 152 | Galvanized | 4                      |
| ASE30X24X6NK   | 30.00 x 24.00 x 6.00 | 762 x 610 x 152 | Painted    | 6                      |
| ASG30X24X6NK   | 30.00 x 24.00 x 6.00 | 762 x 610 x 152 | Galvanized | 6                      |
| ASE30X30X6NK   | 30.00 x 30.00 x 6.00 | 762 x 762 x 152 | Painted    | 8                      |
| ASG30X30X6NK   | 30.00 x 30.00 x 6.00 | 762 x 762 x 152 | Galvanized | 8                      |
| ASE36X24X6NK   | 36.00 x 24.00 x 6.00 | 914 x 610 x 152 | Painted    | 6                      |
| ASG36X24X6NK   | 36.00 x 24.00 x 6.00 | 914 x 610 x 152 | Galvanized | 6                      |
| ASE36X30X6NK   | 36.00 x 30.00 x 6.00 | 914 x 762 x 152 | Painted    | 8                      |
| ASG36X30X6NK   | 36.00 x 30.00 x 6.00 | 914 x 762 x 152 | Galvanized | 8                      |
| ASE36X36X6NK   | 36.00 x 36.00 x 6.00 | 914 x 914 x 152 | Painted    | 8                      |
| ASG36X36X6NK   | 36.00 x 36.00 x 6.00 | 914 x 914 x 152 | Galvanized | 8                      |
| ASE8X8X8NK     | 8.00 x 8.00 x 8.00   | 203 x 203 x 203 | Painted    | 4                      |
| ASG8X8X8NK     | 8.00 x 8.00 x 8.00   | 203 x 203 x 203 | Galvanized | 4                      |
| ASE10X10X8NK   | 10.00 x 10.00 x 8.00 | 254 x 254 x 203 | Painted    | 4                      |
| ASG10X10X8NK   | 10.00 x 10.00 x 8.00 | 254 x 254 x 203 | Galvanized | 4                      |
| ASE12X10X8NK   | 12.00 x 10.00 x 8.00 | 305 x 254 x 203 | Painted    | 4                      |
| ASG12X10X8NK   | 12.00 x 10.00 x 8.00 | 305 x 254 x 203 | Galvanized | 4                      |
| ASE12X12X8NK   | 12.00 x 12.00 x 8.00 | 305 x 305 x 203 | Painted    | 4                      |
| ASG12X12X8NK   | 12.00 x 12.00 x 8.00 | 305 x 305 x 203 | Galvanized | 4                      |
| ASE16X12X8NK   | 16.00 x 12.00 x 8.00 | 406 x 305 x 203 | Painted    | 4                      |
| ASG16X12X8NK   | 16.00 x 12.00 x 8.00 | 406 x 305 x 203 | Galvanized | 4                      |
| ASE18X12X8NK   | 18.00 x 12.00 x 8.00 | 457 x 305 x 203 | Painted    | 4                      |
| ASG18X12X8NK   | 18.00 x 12.00 x 8.00 | 457 x 305 x 203 | Galvanized | 4                      |
| ASE18X18X8NK   | 18.00 x 18.00 x 8.00 | 457 x 457 x 203 | Painted    | 4                      |
| ASG18X18X8NK   | 18.00 x 18.00 x 8.00 | 457 x 457 x 203 | Galvanized | 4                      |
| ASE24X12X8NK   | 24.00 x 12.00 x 8.00 | 610 x 305 x 203 | Painted    | 4                      |
| ASG24X12X8NK   | 24.00 x 12.00 x 8.00 | 610 x 305 x 203 | Galvanized | 4                      |