

Standard Product Selection Matrix

| Description | Sealing Plates ^a Type | Sealing Plates ^a Qty. | 2.50 x 2.50 in. (64 x 64 mm) | 4.00 x 4.00 in. (102 x 102 mm) | 6.00 x 6.00 in. (152 x 152 mm) | 8.00 x 8.00 in. (203 x 203 mm) | 12.00 x 6.00 in. (305 x 152 mm) |
|-------------------------------------------------------------------------------------|----------------------------------|----------------------------------|---------------------------------|-----------------------------------|-----------------------------------|-----------------------------------|------------------------------------|
| 6.00-in. (152-mm) Straight Section | Flat | 1 | F22L06 ^{c,d} | F44L06 ^{c,d} | F66L06 ^{c,d} | F88L06 ^{c,d} | F126L06 ^{c,d} |
| 12.00-in. (305-mm) Straight Section | Flat | 1 | F22L12 ^{c,d} | F44L12 ^{c,d} | F66L12 ^{c,d} | F88L12 ^{c,d} | F126L12 ^{c,d} |
| 24.00-in. (610-mm) Straight Section | Flat | 1 | F22L24 ^{c,d} | F44L24 ^{c,d} | F66L24 ^{c,d} | F88L24 ^{c,d} | F126L24 ^{c,d} |
| 36.00-in. (914-mm) Straight Section | Flat | 1 | F22L36 ^{c,d} | F44L36 ^{c,d} | F66L36 ^{c,d} | F88L36 ^{c,d} | F126L36 ^{c,d} |
| 48.00-in. (1219-mm) Straight Section | Flat | 1 | F22L48 ^{c,d} | F44L48 ^{c,d} | F66L48 ^{c,d} | F88L48 ^{c,d} | F126L48 ^{c,d} |
| 60.00-in. (1524-mm) Straight Section | Flat | 1 | F22L60 ^{c,d} | F44L60 ^{c,d} | F66L60 ^{c,d} | F88L60 ^{c,d} | F126L60 ^{c,d} |
| 120.00-in. (3048-mm) Straight Section | Flat | 1 | F22L120 ^{c,d} | F44L120 ^{c,d} | F66L120 ^{c,d} | F88L120 ^{c,d} | F126L120 ^{c,d} |
| Cutoff Fitting, Lay-In | Flat | 1 | F22LXL | F44LXL | F66LXL | F88LXL | F126LXL |
| Cutoff Fitting, Not Lay-In | 90° Angle | 1 | F22LX | F44LX | F66LX | F88LX | F126LX |
| Telescope Fitting, Lay-In | Special | 1 | F22LA | F44LA | F66LA | F88LA | F126LA |
| Cross Fitting | Flat | 3 | F22LC ^{c,d} | F44LC ^{c,d} | F66LC ^{c,d} | F88LC ^{c,d} | F126LC ^{c,d} |
| 90° Elbow, top opening | Flat | 1 | F22LE9A ^{c,d} | F44LE9A ^{c,d} | F66LE9A ^{c,d} | F88LE9A ^{c,d} | F126LE9A ^{c,d} |
| 90° Elbow, inside opening | Flat | 1 | F22LE9B ^{c,d} | F44LE9B ^{c,d} | F66LE9B ^{c,d} | F88LE9B ^{c,d} | F126LE9B ^{c,d} |
| 90° Elbow, outside opening | Flat | 1 | F22LE9C ^{c,d} | F44LE9C ^{c,d} | F66LE9C ^{c,d} | F88LE9C ^{c,d} | F126LE9C ^{c,d} |
| 90° Elbow, outside top opening | Flat | 2 | — | F44LE9AC ^{c,d} | F66LE9AC ^{c,d} | F88LE9AC ^{c,d} | — |
| 45° Elbow, top opening | Flat | 1 | F22LE45A ^{c,d} | F44LE45A ^{c,d} | F66LE45A ^{c,d} | F88LE45A ^{c,d} | F126LE45A ^{c,d} |
| 45° Elbow, inside opening | Flat | 1 | F22LE45B ^{c,d} | F44LE45B ^{c,d} | F66LE45B ^{c,d} | F88LE45B ^{c,d} | — |
| 45° Elbow, outside opening | Flat | 1 | F22LE45C ^{c,d} | F44LE45C ^{c,d} | F66LE45C ^{c,d} | F88LE45C ^{c,d} | — |
| Tee Fitting, top opening | Flat | 2 | F22LTA ^{c,d} | F44LTA ^{c,d} | F66LTA ^{c,d} | F88LTA ^{c,d} | F126LTA ^{c,d} |
| Tee Fitting, outside top opening | Flat | 2 | F22LTC ^{c,d} | F44LTC ^{c,d} | F66LTC ^{c,d} | F88LTC ^{c,d} | — |
| Junction Box | Flat | 1 | F22LJ ^{c,d} | F44LJ ^{c,d} | F66LJ ^{c,d} | F88LJ ^{c,d} | — |
| Closure Plate | 90° | 1 | F22LP | F44LP | F66LP | F88LP | — |
| Box Connector | 90° | 1 | F22LB | F44LB | F66LB | F88LB | — |
| Reducer 4.00 x 4.00 to 2.50 x 2.50 (102 x 102) to (64 x 64) | None | 0 | — | F44LRE2 | — | — | — |
| Reducer 6.00 x 6.00 to 4.00 x 4.00 (152 x 152) to (102 x 102) | None | 0 | — | — | F66LRE44 ^{c,d} | — | — |
| Reducer 8.00 x 8.00 to 6.00 x 6.00 (203 x 203) to (152 x 152) | None | 0 | — | — | — | F88LRE66 ^d | — |
| Reducer 12.00 x 6.00 to 6.00 x 6.00 (305 x 152) to (152 x 152) | None | 0 | — | — | — | — | F126LRE66 ^{c,d} |
| Reducer 12.00 x 6.00 to 4.00 x 4.00 (305 x 152) to (102 x 102) | None | 0 | — | — | — | — | F126LRE44 ^{c,d} |
| 1.00-in. (25-mm) Nipple | Special | 1 | F22LN1 ^{c,d} | F44LN1 ^{c,d} | F66LN1 ^{c,d} | — | — |
| 2.00-in. (51-mm) Nipple | Special | 1 | F22LN2 ^{c,d} | F44LN2 ^{c,d} | F66LN2 ^{c,d} | — | — |
| 3.00-in. (76-mm) Nipple | Special | 1 | F22LN3 ^{c,d} | F44LN3 ^{c,d} | F66LN3 ^{c,d} | — | — |
| Drop Hanger | None | 0 | F22HD | F44HD | F66HD | F88HD | — |
| Bracket Hanger | None | 0 | F22HB | F44HB | F66HB | F88HB | — |
| Clockwise Transposition Section | Flat | 1 | F22LKT ^{c,d} | F44LKT ^{c,d} | F66LKT ^{c,d} | — | — |
| Counterclockwise Transposition Section | Flat | 1 | F22LKOKT ^{c,d} | F44LKOKT ^{c,d} | F66LKOKT ^{c,d} | — | — |
| 90° Elbow, Clockwise Transposition | Flat | 1 | F22LE9KT ^{c,d} | F44LE9KT ^{c,d} | F66LE9KT ^{c,d} | F88LE9KT ^{c,d} | — |
| 90° Elbow, Counterclockwise Transposition | Flat | 1 | F22LE9KOKT ^{c,d} | F44LE9KOKT ^{c,d} | F66LE9KOKT ^{c,d} | F88LE9KOKT ^{c,d} | — |
| Barrier Kit, bolt-on Each barrier 60.00 in. (1524 mm) | None | 0 | — | F44BK60 | F66BK60 | F88BK60 | F66BK60 |
| Barrier, bracket-mounted ^b Each barrier 60.00 in. (1524 mm) ^b | — | 1 pkg. (5 pcs.) | — | F44B360 | F66B560 | — | — |
| Barrier Brackets, 2 compartment ^b | — | 1 pkg. (5 pcs.) | — | F44BB2C | F66BB2C | — | — |
| Barrier Brackets, 3 compartment ^b | — | 1 pkg. (5 pcs.) | — | F44BB3C | F66BB3C | — | — |
| Flat Sealing Plate ^a | — | — | F22LSGQR | F44LSGQR | F66LSGQR | F88LSGQR | F126LSGQR |
| 90° Angle Sealing Plate ^a | — | — | F22LSAG | F44LSAG | F66LSAG | F88LSAG | F126LSAG |

^a Each sealing plate also includes one gasket and one set of screws to join sections.

^b Package consists of five barriers or five brackets. Each barrier is 60-in. long.

^c Certified by Canadian Standards Association.

^d UL 870