

Standard Product **Polycarbonate**

| Catalog Number | AxBxC mm/in. | Cover Style | External Dimensions L x W mm/in. | Panel | Panel Size D x E mm/in. | Mounting G x H mm/in. | F mm/in. | J mm/in. | K mm/in. | P mm/in. | Q mm/in. | R mm/in. | S mm/in. | U mm/in. |
|----------------|--|-------------|----------------------------------|---------|---------------------------|---------------------------|-------------|------------|------------|-------------|--------------|-------------|--------------|-----------|
| Q554PCD | 53 x 55 x 36 2.09 x 2.17 x 1.42 | Opaque | 55 x 53 2.17 x 2.09 | — | — | 43 x 41 1.69 x 1.61 | 28 1.10 | 25 0.98 | 10 0.39 | 16 0.63 | — | — | — | 2 0.08 |
| Q554PCDCC | 53 x 55 x 36 2.09 x 2.17 x 1.42 | Clear | 55 x 53 2.17 x 2.09 | — | — | 43 x 41 1.69 x 1.61 | 28 1.10 | 25 0.98 | 10 0.39 | 16 0.63 | — | — | — | 2 0.08 |
| Q886PCD | 76 x 74 x 49 2.97 x 2.89 x 1.93 | Opaque | 82 x 80 3.23 x 3.15 | Q88PD | 68 x 55 2.68 x 2.17 | 70 x 50 2.76 x 1.97 | 42 1.65 | 40 1.57 | 15 0.59 | 58 2.28 | 44 1.73 | — | 58 2.28 | 3 0.12 |
| Q886PCDCC | 76 x 74 x 49 2.97 x 2.89 x 1.93 | Clear | 82 x 80 3.23 x 3.15 | Q88PD | 68 x 55 2.68 x 2.17 | 70 x 50 2.76 x 1.97 | 42 1.65 | 40 1.57 | 15 0.59 | 58 2.28 | 44 1.73 | — | 58 2.28 | 3 0.12 |
| Q1286PCD | 114 x 74 x 49 4.47 x 2.89 x 1.93 | Opaque | 120 x 80 4.72 x 3.15 | Q128PD | 91 x 65 3.58 x 2.56 | 108 x 50 4.25 x 1.97 | 42 1.65 | 40 1.57 | 15 0.59 | 58 2.28 | 82 3.23 | — | 96 3.78 | 3 0.12 |
| Q1286PCDCC | 114 x 74 x 49 4.47 x 2.89 x 1.93 | Clear | 120 x 80 4.72 x 3.15 | Q128PD | 91 x 65 3.58 x 2.56 | 108 x 50 4.25 x 1.97 | 42 1.65 | 40 1.57 | 15 0.59 | 58 2.28 | 82 3.23 | — | 96 3.78 | 3 0.12 |
| Q1686PCD | 154 x 74 x 49 6.04 x 2.89 x 1.93 | Opaque | 160 x 80 6.30 x 3.15 | Q168PD | 131 x 65 5.16 x 2.56 | 148 x 50 5.83 x 1.97 | 42 1.65 | 40 1.57 | 15 0.59 | 58 2.28 | 122 4.80 | — | 136 5.35 | 3 0.12 |
| Q1686PCDCC | 154 x 74 x 49 6.04 x 2.89 x 1.93 | Clear | 160 x 80 6.30 x 3.15 | Q168PD | 131 x 65 5.16 x 2.56 | 148 x 50 5.83 x 1.97 | 42 1.65 | 40 1.57 | 15 0.59 | 58 2.28 | 122 4.80 | — | 136 5.35 | 3 0.12 |
| Q12126PCD | 120 x 122 x 56 4.72 x 4.80 x 2.20 | Opaque | 122 x 120 4.80 x 4.72 | Q1212PD | 105 x 93 4.13 x 3.66 | 110 x 90 4.33 x 3.54 | 42 1.65 | 40 1.57 | 15 0.59 | 98 3.86 | 84 3.31 | — | 98 3.86 | 3 0.12 |
| Q12126PCDCC | 120 x 122 x 56 4.72 x 4.80 x 2.20 | Clear | 122 x 120 4.80 x 4.72 | Q1212PD | 105 x 93 4.13 x 3.66 | 110 x 90 4.33 x 3.54 | 42 1.65 | 40 1.57 | 15 0.59 | 98 3.86 | 84 3.31 | — | 98 3.86 | 3 0.12 |
| Q20158PCD | 150 x 200 x 76 5.91 x 7.87 x 2.99 | Opaque | 200 x 150 7.87 x 5.91 | Q2015PD | 170 x 128 6.69 x 5.04 | 188 x 120 7.40 x 4.72 | 62 2.44 | 60 2.36 | 15 0.59 | 118 4.65 | 160 6.30 | 118 4.65 | 176 6.93 | 3 0.12 |
| Q20158PCDCC | 150 x 200 x 76 5.91 x 7.87 x 2.99 | Clear | 200 x 150 7.87 x 5.91 | Q2015PD | 170 x 128 6.69 x 5.04 | 188 x 120 7.40 x 4.72 | 62 2.44 | 60 2.36 | 15 0.59 | 118 4.65 | 160 6.30 | 118 4.65 | 176 6.93 | 3 0.12 |
| Q889PCD | 80 x 82 x 86 3.15 x 3.23 x 3.39 | Opaque | 82 x 80 3.23 x 3.15 | Q88PD | 68 x 55 2.68 x 2.17 | 70 x 50 2.76 x 1.97 | 72 2.83 | 70 2.76 | 15 0.59 | 58 2.28 | 44 1.73 | 37 1.46 | 58 2.28 | 3 0.12 |
| Q889PCDCC | 80 x 82 x 86 3.15 x 3.23 x 3.39 | Clear | 82 x 80 3.23 x 3.15 | Q88PD | 68 x 55 2.68 x 2.17 | 70 x 50 2.76 x 1.97 | 72 2.83 | 70 2.76 | 15 0.59 | 58 2.28 | 44 1.73 | 37 1.46 | 58 2.28 | 3 0.12 |
| Q1289PCD | 113 x 73 x 79 4.45 x 2.87 x 3.11 | Opaque | 120 x 80 4.72 x 3.15 | Q128PD | 91 x 65 3.58 x 2.56 | 108 x 50 4.25 x 1.97 | 72 2.83 | 70 2.76 | 15 0.59 | 58 2.28 | 82 3.23 | — | 96 3.78 | 3 0.12 |
| Q1289PCDCC | 113 x 73 x 79 4.45 x 2.87 x 3.11 | Clear | 120 x 80 4.72 x 3.15 | Q128PD | 91 x 65 3.58 x 2.56 | 108 x 50 4.25 x 1.97 | 72 2.83 | 70 2.76 | 15 0.59 | 58 2.28 | 82 3.23 | — | 96 3.78 | 3 0.12 |
| Q1689PCD | 113 x 73 x 79 4.45 x 2.87 x 3.11 | Opaque | 160 x 80 6.30 x 3.15 | Q168PD | 131 x 65 5.16 x 2.56 | 148 x 50 5.83 x 1.97 | 72 2.83 | 70 2.76 | 15 0.59 | 58 2.28 | 122 4.80 | — | 136 5.35 | 3 0.12 |
| Q1689PCDCC | 113 x 73 x 79 4.45 x 2.87 x 3.11 | Clear | 160 x 80 6.30 x 3.15 | Q168PD | 131 x 65 5.16 x 2.56 | 148 x 50 5.83 x 1.97 | 72 2.83 | 70 2.76 | 15 0.59 | 58 2.28 | 122 4.80 | — | 136 5.35 | 3 0.12 |
| Q12129PCD | 120 x 122 x 86 4.72 x 4.80 x 3.39 | Opaque | 122 x 120 4.80 x 4.72 | Q1212PD | 105 x 93 4.13 x 3.66 | 110 x 90 4.33 x 3.54 | 72 2.83 | 70 2.76 | 15 0.59 | 98 3.86 | 84 3.31 | 3.82 | 97 3.86 | 3 0.12 |
| Q12129PCDCC | 120 x 122 x 86 4.72 x 4.80 x 3.39 | Clear | 122 x 120 4.80 x 4.72 | Q1212PD | 105 x 93 4.13 x 3.66 | 110 x 90 4.33 x 3.54 | 72 2.83 | 70 2.76 | 15 0.59 | 98 3.86 | 84 3.31 | 3.82 | 97 3.86 | 3 0.12 |
| Q20129PCD | 193 x 113 x 79 7.60 x 4.45 x 3.11 | Opaque | 200 x 120 7.87 x 4.72 | Q2012PD | 170 x 100 6.69 x 3.94 | 188 x 90 7.40 x 3.54 | 72 2.83 | 70 2.76 | 15 0.59 | 90 3.54 | 160 6.30 | 40 1.57 | 176 6.93 | 3 0.12 |
| Q20129PCDCC | 193 x 113 x 79 7.60 x 4.45 x 3.11 | Clear | 200 x 120 7.87 x 4.72 | Q2012PD | 170 x 100 6.69 x 3.94 | 188 x 90 7.40 x 3.54 | 72 2.83 | 70 2.76 | 15 0.59 | 90 3.54 | 160 6.30 | 40 1.57 | 176 6.93 | 3 0.12 |
| Q30239PCD | 293 x 223 x 79 11.54 x 8.78 x 3.11 | Opaque | 300 x 230 11.81 x 9.05 | Q3023PD | 265 x 210 10.43 x 8.27 | 288 x 200 11.34 x 7.87 | 73 2.87 | 55 2.17 | 30 1.18 | 198 7.80 | 255 10.04 | 160 6.30 | 275 10.83 | 4 0.16 |
| Q30239PCDCC | 293 x 223 x 79 11.54 x 8.78 x 3.11 | Clear | 300 x 230 11.81 x 9.05 | Q3023PD | 265 x 210 10.43 x 8.27 | 288 x 200 11.34 x 7.87 | 73 2.87 | 55 2.17 | 30 1.18 | 198 7.80 | 255 10.04 | 160 6.30 | 275 10.83 | 4 0.16 |
| Q16129PCD | 153 x 113 x 84 6.02 x 4.45 x 3.29 | Opaque | 160 x 120 6.30 x 4.72 | Q1612PD | 130 x 100 5.12 x 3.94 | 148 x 90 5.83 x 3.54 | 78 3.07 | 60 2.36 | 30 1.18 | 90 3.54 | 120 4.72 | — | 136 5.35 | 3 0.12 |
| Q16129PCDCC | 153 x 113 x 84 6.02 x 4.45 x 3.29 | Clear | 160 x 120 6.30 x 4.72 | Q1612PD | 130 x 100 5.12 x 3.94 | 148 x 90 5.83 x 3.54 | 78 3.07 | 60 2.36 | 30 1.18 | 90 3.54 | 120 4.72 | — | 136 5.35 | 3 0.12 |
| Q24169PCD | 233 x 153 x 84 9.17 x 6.02 x 3.29 | Opaque | 240 x 160 9.45 x 6.30 | Q2416PD | 211 x 148 8.31 x 5.83 | 228 x 130 8.98 x 5.12 | 78 3.07 | 75 2.95 | 15 0.59 | 138 5.43 | 202 7.95 | 75 2.95 | 215 8.46 | 4 0.16 |
| Q24169PCDCC | 233 x 153 x 84 9.17 x 6.02 x 3.29 | Clear | 240 x 160 9.45 x 6.30 | Q2416PD | 211 x 148 8.31 x 5.83 | 228 x 130 8.98 x 5.12 | 78 3.07 | 75 2.95 | 15 0.59 | 138 5.43 | 202 7.95 | 75 2.95 | 215 8.46 | 4 0.16 |
| Q302311PCD | 230 x 300 x 111 9.06 x 11.81 x 4.37 | Opaque | 300 x 230 11.81 x 9.06 | Q3023PD | 265 x 210 10.43 x 8.27 | 288 x 200 11.34 x 7.87 | 98 3.86 | 55 2.17 | 55 2.17 | 198 7.80 | 255 10.04 | 160 6.30 | 275 10.83 | 4 0.16 |
| Q302311PCDCC | 230 x 300 x 111 9.06 x 11.81 x 4.37 | Clear | 300 x 230 11.81 x 9.06 | Q3023PD | 265 x 210 10.43 x 8.27 | 288 x 200 11.34 x 7.87 | 98 3.86 | 55 2.17 | 55 2.17 | 198 7.80 | 255 10.04 | 160 6.30 | 275 10.83 | 4 0.16 |
| Q241612PCD | 160 x 240 x 121 6.30 x 9.45 x 4.76 | Opaque | 240 x 160 9.45 x 6.30 | Q2416PD | 211 x 148 8.31 x 5.83 | 228 x 130 8.98 x 5.12 | 108 4.25 | 75 2.95 | 45 1.77 | 75 2.95 | 202 7.95 | 75 2.95 | 215 8.46 | 4 0.16 |
| Q241612PCDCC | 160 x 240 x 121 6.30 x 9.45 x 4.76 | Clear | 240 x 160 9.45 x 6.30 | Q2416PD | 211 x 148 8.31 x 5.83 | 228 x 130 8.98 x 5.12 | 108 4.25 | 75 2.95 | 45 1.77 | 75 2.95 | 202 7.95 | 75 2.95 | 215 8.46 | 4 0.16 |

A x B x C are internal dimensions.

Purchase panels separately.