

## Ceramalux® Non-ALTO

### Ceramalux 310W Mog ED18 CL

Replace yellow light with crisp, bright white light with just a simple twist! Ideal for industrial applications, warehouses, post top applications and parking lots.

[See full range](#)



[Images](#)

[Diagrams](#)

[Add to ProjectPlanner](#) [Print this page](#) [Contact us](#)



Specifications







[Range](#)

#### Product Data

Product number	134692
Full product name	Ceramalux 310W Mog ED18 CL
Short product name	Ceramalx 310W Mog ED18 CL
Pieces per Sku	1
Skus/Case	12
Bar code on pack	046677134693
Bar code on case	50046677134698
Logistics code(s)	928601108701

[- More info / Hide info](#)

#### Downloads

-  [Leaflet](#)
-  [Family - full data sheet](#)
-  [Material Safety Data Sheets](#)
-  [Warning or caution notice](#)
-  [Product Images](#)
-  [Product Diagrams](#)

#### General Characteristics

Base	Mogul [Mogul]
Base Information	Brass [Brass Base]
Bulb	ED18
Bulb Material	Hard Glass
Bulb Finish	Clear
Operating Position	Universal [Any or Universal (U)]
Main Application	General and Street Lighting
Rated Avg. Life	24000 hr

