

## FLUORESCENT LAMPS

### T12 U-Bent Lamps, Rapid Start T12 Lamps, Preheat T12 Lamps

Watts	Product Number	Symbols, Footnotes	Ordering Code	Pkg. Qty.±	Description	Nom. Length (In.)	Rated Avg. Life (Hrs.) (002)	Approx. Initial Lumens (203204)	Design Lumens (208)	CRI
<b>RAPID START FLUORESCENT LAMPS</b>										
<b>T12 Medium Bipin</b>										
25	27247-6	●	F25T12/CW/RS/EW/ALTO	30	Cool White, 4100K	36	18,000	1950	1650	62
30	31377-5		F30T12/30U/RS	30	Ultralume, 3000K	36	18,000	2400	2160	85
	31381-7	□	F30T12/50U/RS	30	Ultralume, 5000K	36	18,000	2380	2140	85
	31369-2		F30T12/SPEC30/RS	30	SPEC30, 3000K	36	18,000	2350	2080	70
	31371-8	✕	F30T12/SPEC35/RS	30	SPEC35, 3500K	36	18,000	2350	2080	73
	31372-6	✕	F30T12/SPEC41/RS	30	SPEC41, 4100K	36	18,000	2350	2080	70
	31376-7		F30T12/C50/RS	30	Colortone 50, 5000K	36	18,000	1550	1300	92
	37649-1	●	F30T12/D/RS/ALTO	30	Daylight, 6500K	36	18,000	1950	1700	79
	27242-7	●	F30T12/CW/RS/ALTO	30	Cool White, 4100K	36	18,000	2250	1900	62
	13221-7	●	F30T12/WW/RS/ALTO	30	Warm White, 3000K	36	18,000	2300	1950	53

Watts	Product Number	Symbols, Footnotes	Ordering Code	Pkg. Qty.±	Description	Nom. Length (In.)	Rated Avg. Life (Hrs.) (002)	Approx. Initial Lumens (203204)	Design Lumens (208)	CRI
<b>PREHEAT FLUORESCENT LAMPS</b>										
<b>T12 Medium Bipin Linear Fluorescent Lamps</b>										
14	14151-5		F14T12/CW	30	Cool White, 4100K	15	9000	710	590	62
15	14147-3	✕	F15T12/D	30	Daylight, 6500K	18	9000	650	535	79
	14149-9		F15T12/CW	30	Cool White, 4100K	18	9000	800	695	62
20	31399-9		F20T12/30U	30	Ultralume, 3000K	24	9000	1350	1270	85
	31401-3		F20T12/41U	30	Ultralume, 4100K	24	9000	1350	1270	85
	31396-5		F20T12/C50	30	Colortone 50, 5000K	24	9000	850	755	92
	27328-4	●	F20T12/D/ALTO	30	Daylight, 6500K	24	9000	960	960	79
	27332-6	●	F20T12/CW/ALTO	30	Cool White, 4100K	24	9000	1200	1050	62
	27349-0	●	F20T12/WW/ALTO	30	Warm White, 3000K	24	9000	1250	1100	53
	39227-4		F20T12/PLANT	6	Plant Lite, Sleeved	24	9000	600	500	—

For the most current product information go to the e-catalog on [www.philips.com](http://www.philips.com)  
Fluorescent symbol and footnotes located on page 120



T12 Medium Bipin