

Incandescent 20-51

Halogen 52-70

Compact Fluorescent 71-86

Fluorescent 87-120

FLUORESCENT LAMPS

Slimline T12 Lamps

Watts	Product Number	Symbols, Footnotes	Ordering Code	Pkg. Qty.	Description	Nom. Length (In.)	Rated Avg. Life (Hrs.) (202)	Approx. Initial Lumens (203/204)	Design Lumens (208)	CRI
SLIMLINE "LONG LIFE" FLUORESCENT LAMPS										
T12 Single Pin Linear Fluorescent Lamps; Instant Start										
60	14747-0	X ●	F96T12/CW/EW/LL/ALTO	15	Cool White, 4100K	96	18,000	5400	4750	62
	14748-8	X ●	F96T12/841/EW/LL/ALTO	15	TL841, 4100K	96	18,000	5900	5550	85
75	14749-6	●	F96T12/841/LL/ALTO	15	TL841, 4100K	96	18,000	6600	6225	85
SLIMLINE 800 SERIES FLUORESCENT LAMPS										
T12 Single Pin Linear Fluorescent Lamps; Instant Start										
60	14269-5	●	F96T12/830/EW/ALTO	15	TL830, 3000K	96	12,000	5900	5550	85
	14270-3	●	F96T12/835/EW/ALTO	15	TL835, 3500K	96	12,000	5900	5550	85
	14271-1	●	F96T12/841/EW/ALTO	15	TL841, 4100K	96	12,000	5900	5550	85
	14272-9	●	F96T12/850/EW/ALTO	15	TL850, 5000K	96	12,000	5800	5450	85
75	14273-7	●	F96T12/830/ALTO	15	TL830, 3000K	96	12,000	6600	6225	85
	14274-5	●	F96T12/835/ALTO	15	TL835, 3500K	96	12,000	6600	6225	85
	14275-2	●	F96T12/841/ALTO	15	TL841, 4100K	96	12,000	6600	6225	85
	14276-0	●	F96T12/850/ALTO	15	TL850, 5000K	96	12,000	6500	6125	85
SLIMLINE FLUORESCENT LAMPS										
T12 Single Pin Linear Fluorescent Lamps; Instant Start										
30	14140-8	\$	F36T12/CW	30	Cool White, 4100K	36	7500	1850	1630	62
	36609-6	X ●	F48T12/SPEC41/EW/ALTO	15	SPEC41, 4100K	48	9000	2575	2350	70
39	36219-4	●	F48T12/D/ALTO	15	Daylight, 6500K	48	9000	2500	2200	79
	3660-9	●	F48T12/WW/ALTO	15	Warm White, 3000K	48	9000	2950	2650	53
50	35564-4	●	F60T12/D	15	Daylight, 6500K	60	12,000	3150	2850	79
	35563-6	●	F60T12/CW	15	Cool White, 4100K	60	12,000	3450	3050	62
51	35577-6	●	F64T12/D	15	Daylight, 6500K	64	12,000	3200	2800	79
56	36623-7	X ●	F72T12/SPEC35/ALTO	15	SPEC35, 3500K	72	12,000	4700	4400	73
	36985-0	●	F72T12/D/ALTO	15	Daylight, 6500K	72	12,000	3800	3350	79
60	36989-2	●	F72T12/CW/ALTO	15	Cool White, 4100K	72	12,000	4450	3900	62
	36661-7	●	F72T12/WW/ALTO	15	Warm White, 3000K	72	12,000	4550	4000	53
60	36624-5	X \$ ●	F96T12/30U/EW/ALTO	15	Ultralume, 3000K	96	12,000	5900	5550	85
	36630-2	X \$ ●	F96T12/SPEC30/EW/ALTO	15	SPEC30, 3000K	96	12,000	5750	5400	70
	36654-2	●	F96T12/DX/EW/ALTO	15	Daylight Deluxe, 6500K	96	12,000	4200	3675	84
	25840-0	●	F96T12/CW/EW/ALTO	15	Cool White, 4100K	96	12,000	5400	4750	62
	36656-7	●	F96T12/WW/EW/ALTO	15	Warm White, 3000K	96	12,000	5500	4850	53
75	36650-0	X ●	F96T12/SPEC41/ALTO	15	SPEC41, 4100K	96	12,000	6425	6050	70
	34170-1	●	F96T12/C50	15	Colortone 50, 5000K	96	12,000	4650	4200	92
	37282-1	●	F96T12/DX/ALTO	15	Daylight Deluxe, 6500K	96	12,000	4500	3950	84

For the most current product information go to the e-catalog on www.philips.com
Fluorescent symbol and footnotes located on page 120



T12 Single Pin