



Philips HID
Metal Halide

400W

ED37 Mogul Base

046677253653

Many models for indoor and outdoor applications

Philips High Intensity Discharge light bulbs offer unbeatable light quality and consistent performance.

Premium quality

- Provides dusk-to-dawn lighting in outdoor security fixtures

PHILIPS
sense and simplicity

Metal Halide
400W ED37 Mogul Base

046677253653

Specifications

Technical specifications

- Indoor
- Lamp holder: ED37
- Location: Indoor warehouse, Outdoor
- Number of lamps: 1

- Outdoor
- Placement: Ceiling fixtures, Outdoor Security
- Power supply: 120 V
- Type: General lighting
- Wattage: 400 W

Highlights

For Outdoor use

Provides dusk-to-dawn lighting in outdoor security fixtures



Issue date 2011-11-29

Version: 1.0.0

12 NC: 9286 011 51400
UPC: 0 46677 25365 3

© 2011 Koninklijke Philips Electronics N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips
Electronics N.V. or their respective owners.

www.philips.com