

HALOGEN LAMPS

Single-Ended Linear, Double-Ended Linear, Low-Voltage Capsule Lamps

Watts	Bulb	Base	Product Number	Symbols, Footnotes	Ordering Code	Volts	Pkg. Qty.	Description	Class, Filament	MOL (in.)	Rated Avg. Life (Hrs.)#3	Approx. MBCP*	Lumens
HALOGEN SINGLE-ENDED LINEAR LAMPS BLISTER-CARDED (95)													
50	T4	Mini-Can	20347-1		BC 50Q/CL	120	12	Blister Card	C, CC-8	2K	1000	—	500
75	T4	Mini-Can	20359-6		BC 75Q/CL	120	12	Blister Card	C, CC-8	3	1000	—	1050
100	T4	Mini-Can	20350-5		BC 100Q/CL ESN	120	12	Blister Card	C, CC-8	2.9K	1000	—	1600
150	T4	Mini-Can	20354-7		BC 150Q/CL ETG	120	12	Blister Card	C, CC-8	3	1000	—	2800
HALOGEN SINGLE-ENDED LINEAR LAMPS (95)													
100	T4	D.C. Bay	44278-0		100Q/CL/DC ESR	120	12	Clear	C, CC-8	2K	1000	—	1600
150	T4	Mini-Can	29856-2		150Q ETH	120	12	Frost	C, CC-8	3	1000	—	2700
			20049-3		150Q/CL	130	12	Clear	C, CC-8	3	1000	—	2800
	T4	D.C. Bay	26676-7		150Q/CL/DC ETC	120	12	Clear	C, CC-8	2K	1000	—	2800
250	T4	Mini-Can	29850-5		150Q/DC ETF	120	12	Frost	C, CC-8	2K	1000	—	2700
			14668-8		250Q/CL BHT	120	12	Clear	C, CC-8	3K	1000	—	5000
	T4	D.C. Bay	14667-0		250Q/CL	130	12	Clear	C, CC-8	3K	1000	—	5000
			14666-2		250Q/CL/DC ESS	120	12	Clear	C, CC-8	3	1000	—	5000
500	T4	Mini-Can	14669-6		250Q/CL/DC	130	12	Clear	C, CC-8	3	1000	—	5000
			38079-0		500Q/CL EVR	120	12	Clear	C, C-8	3K	2000	—	10,000
750	T5	Med.2-Pin	26972-0		750Q/CL BHG	120	24	Clear	C, CC-8	4K	2000	—	15,000
HALOGEN DOUBLE-ENDED LINEAR LAMP BLISTER-CARDED (99)													
100	T3	RSC	20352-1		BC 100T3Q/CL	120	12	Blister Card	C, C-8	3K	2000	—	1400
150	T3	RSC	20353-9		BC 150T3Q/CL	120	12	Blister Card	C, C-8	3K	2000	—	2400
			20343-0		BC 150T3Q/CL LONG	120	12	Blister Card	C, C-8	4K	1500	—	2400
250	T3	RSC	20360-4		BC 250T3Q/CL	120	12	Blister Card	C, C-8	3K	1500	—	4000
300	T3	RSC	20355-4		BC 300T3Q/CL	120	12	Blister Card	C, C-8	4K	2000	—	5200
			20336-4		BC 300T3Q/CL/TP	120	12	Blister Card	C, C-8	4K	2000	—	5200
500	T3	RSC	20356-2		BC 500T3Q/CL	120	12	Blister Card	C, C-8	4K	2000	—	9500
			20341-4		BC 500T3Q/CL/TP	120	12	Blister Card	C, C-8	4K	2000	—	9500
HALOGEN DOUBLE-ENDED LINEAR LAMP (99)													
300	T3	RSC	39282-9		300T3Q/CL BHM	120	12	Clear	C, C-8	4K	2000	—	5200
500	T3	RSC	13223-3		500T3Q/CL	125-130	12	Clear	C, C-8	4K	2000	—	9200
			20010-5		500T3Q/CL FCL	120	12	Clear	C, C-8	4K	2000	—	9500
1000	T3	RSC	15040-9		1000T3Q/CL	240	12	Clear	C, C-8	10K	2000	—	21,500
1500	T3	RSC	15039-1		1500T3Q/CL	277	12	Clear	C, C-8	10K	2000	—	33,000
			13226-6		1500T3Q/CL	240	12	Clear	C, C-8	10K	2000	—	32,250
HALOGEN MAINS-VOLTAGE CAPSULE LAMP BLISTER-CARDED (95)													
35	T4	GY8.6	20345-5		BC 35W/T4/120V/CAPSULE	120	12	Blister Card	C, CC2V	1.9K	2500	—	400
50	T4	GY8.6	20348-9		BC 50W/T4/120V/CAPSULE	120	12	Blister Card	C, C-8	2K	2500	—	600
75	T4	GY8.6	20349-7		BC 75W/T4/120V/CAPSULE	120	12	Blister Card	C, C-8	2K	2000	—	1200
100	T4	GY8.6	20346-3		BC 100W/T4/120V/CAPSULE	120	12	Blister Card	C, C-8	2K	2500	—	1650

For the most current product information go to the e-catalog on www.philips.com
Halogen symbol and footnotes located on page 70

