

Incandescent 20-51

Halogen 52-70

Compact Fluorescent 71-86

Fluorescent 87-120

## HALOGEN LAMPS

### PAR20, PAR30L, PAR30S Lamps

Watts	Bulb	Base	Product Number	Symbols, Footnotes	Ordering Code	Volts	Pkg. Qty.†	Description	Class, Filament	MOL (In.)	Rated Avg. Life (Hrs.)@93	Approx. MBCP*	Lumens
<b>HALOGEN PAR20 LAMPS 130V WISO REFLECTOR (82, 86)</b>													
50	PAR20	Med.	13846-1	\$	50PAR20/HAL/SP10	130	15	Spot 10" Ratings @ 120V=44W	C, CC-8	3½	2000 4000	4000 3320	550 420
			22921-1	\$	50PAR20/HAL/FL25	130	15	Flood 25" Ratings @ 120V=44W	C, CC-8	3½	2000 4000	1100 880	550 420
<b>HALOGEN PAR30L LONG NECK LAMP WISO REFLECTOR (82, 86)</b>													
50	PAR30L	Med.	22922-9	Ⓢ	50PAR30L/HAL/SP10	120	15	Spot 10"	C, CC-8	4½	3000	5500	590
			22923-7	Ⓢ	50PAR30L/HAL/WSP16	120	15	Wide Spot 16"	C, CC-8	4½	3000	3500	590
			22925-2	Ⓢ	50PAR30L/HAL/FL25	120	15	Flood 25"	C, CC-8	4½	3000	2100	590
			22927-8	Ⓢ	50PAR30L/HAL/WFL40	120	15	Wide Flood 40"	C, CC-8	4½	3000	950	590
75	PAR30L	Med.	22930-2	Ⓢ	75PAR30L/HAL/SP10	120	15	Spot 10"	C, CC-8	4½	3000	12,300	1000
			22934-4	Ⓢ	75PAR30L/HAL/WSP16	120	15	Wide Spot 16"	C, CC-8	4½	3000	6700	1000
			22941-9	Ⓢ	75PAR30L/HAL/FL25	120	15	Flood 25"	C, CC-8	4½	3000	4100	1000
			22944-3	Ⓢ	75PAR30L/HAL/WFL40	120	15	Wide Flood 40"	C, CC-8	4½	3000	1650	1000
<b>HALOGEN PAR30L LONG NECK LAMP 130V WISO REFLECTOR (82, 86)</b>													
50	PAR30L	Med.	22926-0	\$ Ⓢ	50PAR30L/HAL/FL25	130	15	Flood 25" Ratings @ 120V=44W	C, CC-8	4½	2000 4000	2300 1960	630 470
			22928-6	\$ Ⓢ	50PAR30L/HAL/WFL40	130	15	Wide Flood 40" Ratings @ 120V=44W	C, CC-8	4½	2000 4000	1050 840	630 470
75	PAR30L	Med.	13848-7	\$ Ⓢ	75PAR30L/HAL/SP10	130	15	Spot 10" Ratings @ 120V=66W	C, CC-8	4½	2500 5000	13,000 10,400	1050 780
			22943-5	\$ Ⓢ	75PAR30L/HAL/FL25	130	15	Flood 25" Ratings @ 120V=66W	C, CC-8	4½	2500 5000	4200 3360	1050 780
			22945-0	\$ Ⓢ	75PAR30L/HAL/WFL40	130	15	Wide Flood 40" Ratings @ 120V=66W	C, CC-8	4½	2500 5000	1750 1400	1050 780
<b>HALOGEN PAR30S SHORT LAMP WISO REFLECTOR (82, 86)</b>													
50	PAR30S	Med.	26349-1	Ⓢ	50PAR30S/HAL/SP10	120	15	Spot 10"	C, CC-8	3½	3500	5800	610
			26358-2	Ⓢ	50PAR30S/HAL/FL25	120	15	Flood 25"	C, CC-8	3½	3500	1800	610
			26364-0	Ⓢ	50PAR30S/HAL/WFL40	120	15	Wide Flood 40"	C, CC-8	3½	3500	900	610
60	PAR30S	Med.	35751-7	Ⓢ	60PAR30S/HAL/SP10	120	15	Spot 10"	C, CC-8	3½	3000	8000	800
			35753-3	Ⓢ	60PAR30S/HAL/FL25	120	15	Flood 25"	C, CC-8	3½	3000	2500	800
75	PAR30S	Med.	28479-4	Ⓢ	75PAR30S/HAL/SP10	120	15	Spot 10"	C, CC-8	3½	3500	9600	1050
			28488-5	Ⓢ	75PAR30S/HAL/FL25	120	15	Flood 25"	C, CC-8	3½	3500	3850	1050
			28491-9	Ⓢ	75PAR30S/HAL/WFL40	120	15	Wide Flood 40"	C, CC-8	3½	3500	1650	1050

For the most current product information go to the e-catalog on [www.philips.com](http://www.philips.com)  
Halogen symbol and footnotes located on page 70



60 Philips Lighting Company SAGI 00 2008-2009