

HALOGEN LAMPS

Single-Ended Linear, Double-Ended Linear, Low-Voltage Capsule Lamps

| Watts | Bulb | Base | Product Number | Symbols, Footnotes | Ordering Code | Volts | Pkg. Qty. | Description | Class, Filament | MOL (In.) | Rated Avg. Life (Hrs.)#3 | Approx. MBCP* | Lumens |
|---|------|-----------|----------------|--------------------|-------------------------|---------|-----------|--------------|-----------------|-----------|--------------------------|---------------|--------|
| HALOGEN SINGLE-ENDED LINEAR LAMPS BLISTER-CARDED (95) | | | | | | | | | | | | | |
| 50 | T4 | Mini-Can | 20347-1 | | BC 50Q/CL | 120 | 12 | Blister Card | C, CC-8 | 2K | 1000 | — | 500 |
| 75 | T4 | Mini-Can | 20359-6 | | BC 75Q/CL | 120 | 12 | Blister Card | C, CC-8 | 3 | 1000 | — | 1050 |
| 100 | T4 | Mini-Can | 20350-5 | | BC 100Q/CL ESN | 120 | 12 | Blister Card | C, CC-8 | 2.9K | 1000 | — | 1600 |
| 150 | T4 | Mini-Can | 20354-7 | | BC 150Q/CL ETG | 120 | 12 | Blister Card | C, CC-8 | 3 | 1000 | — | 2800 |
| HALOGEN SINGLE-ENDED LINEAR LAMPS (95) | | | | | | | | | | | | | |
| 100 | T4 | D.C. Bay | 44278-0 | | 100Q/CL/DC ESR | 120 | 12 | Clear | C, CC-8 | 2K | 1000 | — | 1600 |
| 150 | T4 | Mini-Can | 29856-2 | | 150Q ETH | 120 | 12 | Frost | C, CC-8 | 3 | 1000 | — | 2700 |
| | | | 20049-3 | | 150Q/CL | 130 | 12 | Clear | C, CC-8 | 3 | 1000 | — | 2800 |
| | T4 | D.C. Bay | 26676-7 | | 150Q/CL/DC ETC | 120 | 12 | Clear | C, CC-8 | 2K | 1000 | — | 2800 |
| 250 | T4 | Mini-Can | 29850-5 | | 150Q/DC ETF | 120 | 12 | Frost | C, CC-8 | 2K | 1000 | — | 2700 |
| | | | 14668-8 | | 250Q/CL BHT | 120 | 12 | Clear | C, CC-8 | 3K | 1000 | — | 5000 |
| | T4 | D.C. Bay | 14667-0 | | 250Q/CL | 130 | 12 | Clear | C, CC-8 | 3K | 1000 | — | 5000 |
| | | | 14666-2 | | 250Q/CL/DC ESS | 120 | 12 | Clear | C, CC-8 | 3 | 1000 | — | 5000 |
| 500 | T4 | Mini-Can | 14669-6 | | 250Q/CL/DC | 130 | 12 | Clear | C, CC-8 | 3 | 1000 | — | 5000 |
| | | | 38079-0 | | 500Q/CL EVR | 120 | 12 | Clear | C, C-8 | 3K | 2000 | — | 10,000 |
| 750 | T5 | Med.2-Pin | 26972-0 | | 750Q/CL BHG | 120 | 24 | Clear | C, CC-8 | 4K | 2000 | — | 15,000 |
| HALOGEN DOUBLE-ENDED LINEAR LAMP BLISTER-CARDED (99) | | | | | | | | | | | | | |
| 100 | T3 | RSC | 20352-1 | | BC 100T3Q/CL | 120 | 12 | Blister Card | C, C-8 | 3K | 2000 | — | 1400 |
| 150 | T3 | RSC | 20353-9 | | BC 150T3Q/CL | 120 | 12 | Blister Card | C, C-8 | 3K | 2000 | — | 2400 |
| | | | 20343-0 | | BC 150T3Q/CL LONG | 120 | 12 | Blister Card | C, C-8 | 4K | 1500 | — | 2400 |
| 250 | T3 | RSC | 20360-4 | | BC 250T3Q/CL | 120 | 12 | Blister Card | C, C-8 | 3K | 1500 | — | 4000 |
| 300 | T3 | RSC | 20355-4 | | BC 300T3Q/CL | 120 | 12 | Blister Card | C, C-8 | 4K | 2000 | — | 5200 |
| | | | 20336-4 | | BC 300T3Q/CL/TP | 120 | 12 | Blister Card | C, C-8 | 4K | 2000 | — | 5200 |
| 500 | T3 | RSC | 20356-2 | | BC 500T3Q/CL | 120 | 12 | Blister Card | C, C-8 | 4K | 2000 | — | 9500 |
| | | | 20341-4 | | BC 500T3Q/CL/TP | 120 | 12 | Blister Card | C, C-8 | 4K | 2000 | — | 9500 |
| HALOGEN DOUBLE-ENDED LINEAR LAMP (99) | | | | | | | | | | | | | |
| 300 | T3 | RSC | 39282-9 | | 300T3Q/CL BHM | 120 | 12 | Clear | C, C-8 | 4K | 2000 | — | 5200 |
| 500 | T3 | RSC | 13223-3 | | 500T3Q/CL | 125-130 | 12 | Clear | C, C-8 | 4K | 2000 | — | 9200 |
| | | | 20010-5 | | 500T3Q/CL FCL | 120 | 12 | Clear | C, C-8 | 4K | 2000 | — | 9500 |
| 1000 | T3 | RSC | 15040-9 | | 1000T3Q/CL | 240 | 12 | Clear | C, C-8 | 10K | 2000 | — | 21,500 |
| 1500 | T3 | RSC | 15039-1 | | 1500T3Q/CL | 277 | 12 | Clear | C, C-8 | 10K | 2000 | — | 33,000 |
| | | | 13226-6 | | 1500T3Q/CL | 240 | 12 | Clear | C, C-8 | 10K | 2000 | — | 32,250 |
| HALOGEN MAINS-VOLTAGE CAPSULE LAMP BLISTER-CARDED (95) | | | | | | | | | | | | | |
| 35 | T4 | GY8.6 | 20345-5 | | BC 35W/T4/120V/CAPSULE | 120 | 12 | Blister Card | C, CC2V | 1.9K | 2500 | — | 400 |
| 50 | T4 | GY8.6 | 20348-9 | | BC 50W/T4/120V/CAPSULE | 120 | 12 | Blister Card | C, C-8 | 2K | 2500 | — | 600 |
| 75 | T4 | GY8.6 | 20349-7 | | BC 75W/T4/120V/CAPSULE | 120 | 12 | Blister Card | C, C-8 | 2K | 2000 | — | 1200 |
| 100 | T4 | GY8.6 | 20346-3 | | BC 100W/T4/120V/CAPSULE | 120 | 12 | Blister Card | C, C-8 | 2K | 2500 | — | 1650 |

For the most current product information go to the e-catalog on www.philips.com
Halogen symbol and footnotes located on page 70

