

Incandescent 20-51

Halogen 52-70

Compact Fluorescent 71-86

Fluorescent 87-120

FLUORESCENT LAMPS

Rapid Start T8 Lamps, Preheat T8 Lamps

Watts	Product Number	Symbols, Footnotes	Ordering Code	Pkg. Qty.†	Description	Nom. Length (In.)	Rated Average Life		Approx. Initial Lumens (200,204)	Design Lumens (208)	CRI
							3 Hr.	12 Hr.			
RAPID START FLUORESCENT LAMPS											
T8 Medium Bipin-High CRI											
17	22154-9	\$	F17T8/TL950	25	TL 950,5000K	24	20,000	20,000	910	850	98
25	22159-8	\$	F25T8/TL950	25	TL 950,5000K	36	20,000	20,000	1550	1450	98
32	20904-9	\$	F32T8/TL930	25	TL 930,3000K	48	20,000	20,000	2000	1860	95
	20905-6	\$	F32T8/TL950	25	TL 950,5000K	48	20,000	20,000	2000	1860	98
TL-D RAPID START FLUORESCENT LAMPS—FOR OPERATION ON EUROPEAN BALLAST											
T8 Medium Bipin-High CRI											
36	29189-8	†	TLD36W/84QNG	25	TL840,4000K	48	20,000		3350	3100	82
58	29184-9	†	TLD58W/84QNG	25	TL840,4000K	60	20,000		5200	4300	82
70	29186-4	†	TLD70W/84QNG	25	TL840,4000K	72	20,000		6200	5100	82
PREHEAT FLUORESCENT LAMPS											
T8 Medium Bipin Linear Fluorescent Lamps; Requires Use of Starters (202)											
15	37823-2	●	F15T8D/ALTO	24	Daylight, 6500K	18	7500		750	660	79
	38298-6	●	F15T8/VWW/ALTO	24	Warm White, 3000K	18	7500		870	740	53
	36720-1	●	F15T8/CW/ALTO	24	Cool White, 4100K	18	7500		870	765	62
	36436-4		F15T8/CW BULK	96	Cool White, 4100K	18	7500		850	750	62
	39226-6		F15T8/PLANT	6	Plant Lite, Sleeve d	18	7500		410	NA	NA
30	26063-8	●	F30T8/D/ALTO	24	Daylight, 6500K	36	7500		1500	1350	79
	38691-2	●	F30T8/CW/ALTO	24	Cool White, 4100K	36	7500		2200	2000	62

For the most current product information go to the e-catalog on www.philips.com
Fluorescent symbol and footnotes located on page 120



T8 Medium Bipin