



Philips EcoVantage
Energy saving household
light

72W

A19 Medium Base

046677409821

Savings without sacrifice

Meets federal energy efficiency guidelines

Philips EcoVantage bulbs reduce energy consumption without sacrificing the qualities of a traditional bulb. Fully dimmable, they provide a bright white, energy saving light to enhance your home, while helping preserve our energy resources.

Use in any room in your home

- For use in table lamps, floor lamps and pendant fixtures

Light effect

- Provides a comfortable and relaxing environment

Energy efficient

- Replaces a 100W incandescent light bulb

Sustainable choice

- Reduce greenhouse gases and shrink your carbon footprint
- Contains no mercury

PHILIPS

sense and simplicity

Energy saving household light
72W A19 Medium Base

Specifications

Technical specifications

- Dimmable
- Indoor
- Lamp holder: A19
- Location: Bathroom, Bedroom, Dining room, Hallway, Kitchen, Living room, Office

- Number of lamps: 2
- Placement: Ceiling fixtures, Floor lamps, Pendant fixtures, Table lamps
- Power supply: 120 V
- Type: General lighting
- Wattage: 72 W

046677409821

Highlights

Ideal for general room light

For use in table lamps, floor lamps and pendant fixtures

Soft white light

Provides a comfortable and relaxing environment

Replace your current bulb

Replaces a 100W incandescent light bulb

Better for the environment

Reduce greenhouse gases and shrink your carbon footprint

Contains no mercury

Contains no mercury



Issue date 2011-11-29

Version: 1.0.0

12 NC: 9257 018 36300
UPC: 0 46677 40982 1

© 2011 Koninklijke Philips Electronics N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips
Electronics N.V. or their respective owners.

www.philips.com

* Compared to a 100W A19 bulb with 1440 lumens, the 72W A19 EcoVantage with 1490 lumens saves 28% energy.