

## FLUORESCENT LAMPS

### PLUS 800 Series T8 Lamps, PLUS 700 Series T8 Lamps

Watts	Product Number	Symbols, Footnotes	Ordering Code	Pkg. Qty.±	Description	Nom. Length (In.)	Rated Average Life		Approx. Initial Lumens (200,204)	Design Lumens (208,239)	CRI
							3 Hr.	12 Hr.			
<b>PLUS 800 SERIES LONG LIFE T8 FLUORESCENT LAMPS</b>											
<b>T8 Medium Bipin Featuring ALTO II™ Technology and HI-VISION® Phosphor</b>											
15	38419-8	◆ □ \$ ① ●	F15T8/TL865/PLUS/ALTO	24	TL 865,6500K	18	30,000	36,000	975	925	85
17	14552-4	\$ ① ●	F17T8/TL830/PLUS/ALTO	25	TL 830,3000K	24	30,000	36,000	1400	1300	85
	14553-2	\$ ① ●	F17T8/TL835/PLUS/ALTO	25	TL 835,3500K	24	30,000	36,000	1400	1300	85
	14554-0	\$ ① ●	F17T8/TL841/PLUS/ALTO	25	TL 841,4100K	24	30,000	36,000	1400	1300	85
	14555-7	\$ ① ●	F17T8/TL850/PLUS/ALTO	25	TL 850,5000K	24	30,000	36,000	1300	1235	82
	38215-0	\$ ① ●	F17T8/TL865/PLUS/ALTO	25	TL 865,6500K	24	30,000	36,000	1275	1210	85
25	14556-5	\$ ① ●	F25T8/TL830/PLUS/ALTO	25	TL 830,3000K	36	30,000	36,000	2225	2050	85
	14557-3	\$ ① ●	F25T8/TL835/PLUS/ALTO	25	TL 835,3500K	36	30,000	36,000	2225	2050	85
	14558-1	\$ ① ●	F25T8/TL841/PLUS/ALTO	25	TL 841,4100K	36	30,000	36,000	2225	2050	85
	14559-9	\$ ① ●	F25T8/TL850/PLUS/ALTO	25	TL 850,5000K	36	30,000	36,000	2150	2020	82
	38258-0	\$ ① ●	F25T8/TL865/PLUS/ALTO	25	TL 865,6500K	36	30,000	36,000	2125	2000	85
32	36000-8	\$ ① ●	F32T8/TL830/PLUS/ALTO	25	TL 830,3000K	48	30,000	36,000	2950	2800	85
	36001-6	\$ ① ●	F32T8/TL835/PLUS/ALTO	25	TL 835,3500K	48	30,000	36,000	2950	2800	85
	36002-4	\$ ① ●	F32T8/TL841/PLUS/ALTO	25	TL 841,4100K	48	30,000	36,000	2950	2800	85
	13686-1	\$ ① ●	F32T8/TL841/PLUS/ALTO PLZ	1350	TL 841,4100K	48	30,000	36,000	2950	2800	85
	36003-2	\$ ① ●	F32T8/TL850/PLUS/ALTO	25	TL 850,5000K	48	30,000	36,000	2850	2710	82
	38261-4	\$ ① ●	F32T8/TL865/PLUS/ALTO	25	TL 865,6500K	48	30,000	36,000	2750	2610	82

#### PLUS 700 SERIES LONG LIFE T8 FLUORESCENT LAMPS

T8 Medium Bipin Featuring ALTO II™ Technology and HI-VISION® Phosphor

32	36004-0	\$ ① ●	F32T8/TL730/PLUS/ALTO	25	TL 730,3000K	48	30,000	36,000	2800	2660	78
	36005-7	\$ ① ●	F32T8/TL735/PLUS/ALTO	25	TL 735,3500K	48	30,000	36,000	2800	2660	78
	38383-6	\$ ① ●	F32T8/TL735/PLUS/ALTO PLZ	1350	TL 735,3500K	48	30,000	36,000	2800	2660	78
	36013-1	\$ ① ●	F32T8/TL741/PLUS/ALTO	25	TL 741,4100K	48	30,000	36,000	2800	2660	78
	38384-4	\$ ① ●	F32T8/TL741/PLUS/ALTO PLZ	1350	TL 741,4100K	48	30,000	36,000	2800	2660	78
	36014-9	\$ ① ●	F32T8/TL750/PLUS/ALTO	25	TL 750,5000K	48	30,000	36,000	2700	2550	78

For the most current product information go to the e-catalog on [www.philips.com](http://www.philips.com)  
Fluorescent symbol and footnotes located on page 120

**PHILIPS PLUS T8**  
Warranty Period: 36 months\*

\* Certain limitations and conditions apply. See Philips for further warranty details.

