

MasterColor® CDM ED17 Protected

MasterColor CDM 150W/940 Med ED17P CO ALTO+FB

Direct retrofit with immediate energy savings! Range of protected, high-efficiency long life ceramic metal halide lamps with a stable color over lifetime and a crisp, sparkling light to be used in open fixtures.



Product data

• General Characteristics

Base	Medium [Single Contact Medium Screw]
Base Information	Brass [Brass Base]
Bulb	ED17P [Protected]
Bulb Material	Hard Glass
Bulb Finish	Coated
Operating Position	Universal [Any or Universal (U)]
Main Application	General Lighting
RatedAvgLife(See Family Notes)	20000 hr

• Light Technical Characteristics

Color Code	940 [CCT of 4000K]
Color Rendering Index	90 (min), 92 (nom) Ra8
Color Designation	Deluxe Cool White
Color Temperature	4000 K
Color Temperature technical	3900 K
Chromaticity Coordinate X	386 -
Chromaticity Coordinate Y	377 -
Initial Lumens	11000 Lm
Luminous Efficacy Lamp	72 Lm/W
Lumen Maintenance 2000h	88 %
Lumen Maintenance 5000h	78 %
Design Mean Lumens	8250 Lm

• Electrical Characteristics

Watts	150 W
-------	-------

Lamp Voltage	95 V
Lamp Current	1.8 A
Ignition Time	10 (max) s
Ignition Supply Voltage	235 V
Re-ignition Time [min]	12 (max) min

• Environmental Characteristics

Mercury (Hg) Content	11.4 (max) mg
----------------------	---------------

• UV-related Characteristics

PET (NIOSH)	304 h.klx
Damage Factor D/fc	0.281 -

• Luminaire Design Requirements

Cap-Base Temperature	190 (max) C
Bulb Temperature	400 (max) C

• Product Dimensions

Light Center Length L	3.438 in
Max Overall Length (MOL) - C	5.438 (max) in
Diameter D	2.125 in

• Footnotes

Footnotes HID	902 [Exclusive to Philips Lighting Company.]
---------------	--

PHILIPS
sense and simplicity

• Product Data

Product number 377267
 Full product name MasterColor CDM 150W/940 Med ED17P CO ALTO+FB
 Short product name CDM 150W/940 Med ED17P CO ALTO+FB
 Pieces per Sku 1

eop_pck_cfg 12
 Skus/Case 12
 Bar code on pack 46677377267
 Bar code on case 50046677377262
 Logistics code(s) 928601132801
 eop_net_weight_pp 0.001 kg

Warnings and Safety


- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will

remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)

Dimensional drawing

E26, ED-17P

Product	C (Max)	D (Norm)
MHC P 150W/940 E26 ED17P CO U ALTO+FB	5.438	2.125



E26



© 2012 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2012, August 4
data subject to change