

39 Watt, 120 Volt Halogen PAR20 Flood

Ordering Code: **39PAR20/EV/FL25 (120V)**



Product Details

| | |
|--------------------------------|--------------------------|
| Brand | Philips Lighting Company |
| Energy Used | 39 Watts |
| Volts | 120 |
| Bulb Shape | PAR-20 |
| Base | Medium (E26) |
| Beam Spread | 25° |
| Class and Filament | C, CC-8 |
| Diameter (in) | 2.5 |
| Length (in) | 3.35 |
| Average Rated Life (hr) | 1100 |
| Light Output | 500 Lumens |
| Finish | Clear |
| Bulb Technology | Halogen |

Philips brand EcoVantage PAR20 halogen narrow flood. 39 Watts and 120 volts for more power and light.

- Halogen lights provide brighter, whiter light than incandescent bulbs, while maintaining outstanding color rendering
- Flood means more focused beam of light. Lamp can be further away and still light the area effectively
- Perfect for art galleries and retail applications where light quality is important