

Philips EcoVantage PAR  
Halogen Lamps

*Ideal for retail and  
commercial indoor and  
outdoor applications*

EcoVantage



## Put people and merchandise in the best light

**Philips EcoVantage PAR Lamps** are an economical solution providing bright, white light with excellent beam qualities for accent or ambient lighting.

### Benefits

- Inexpensive initial solution for PAR sockets
- Bright white light brightens merchandise
- Meet upcoming legislation requirements for reflector lamps

### Features

- Offered in PAR20, PAR30S, PAR30L, PAR38
- 1100 hour rated average life\*
- Optimized coil and burner design allows for clear, crisp lighting effects with excellent color rendering.
- Available in a variety of wattages and beam angles

\* Rated average life is the time in hours at which 50% of the lamps will be operational and 50% will not.

**PHILIPS**

# Philips EcoVantage PAR Halogen Lamps

## Electrical and Technical Data (Subject to change without notice)

Product Number	Ordering Code	Nom. Watts	Volts	Pack. Qty.	Description	Rated Avg. Life (Hrs.) <sup>1</sup>	Rated Avg. Life (Yrs.) <sup>2</sup>	Approx. MBCP <sup>3</sup>	Lumens	Color Temp (K)	CRI	Est. Energy Cost <sup>4</sup>
<b>EcoVantage PAR20 Lamps</b>												
42512-4	39PAR20/EVP/SP10 120V	39	120		Halogen Spot 10°	1100	1.0	3800	500	3000	100	\$4.70
42520-7	39PAR20/EVP/FL25 120V	39	120		Halogen Flood 25°	1100	1.0	850	500	3000	100	\$4.70
<b>EcoVantage PAR30 Long Lamps</b>												
42887-0	39PAR30L/EVP/FL25 120V 15/1	39	120		Halogen Flood 25°	1100	1.0	2000	520	2900	100	\$4.70
42892-0	53PAR30L/EVP/FL25 120V 15/1	53	120		Halogen Flood 25°	1100	1.0	3500	920	2900	100	\$6.38
42895-2	53PAR30L/EVP/WFL40 120V 15/1	53	120		Halogen Wide Flood 40°	1100	1.0	1400	920	2900	100	\$6.38
<b>EcoVantage PAR30 Short Lamps</b>												
42891-2	39PAR30S/EVP/SP10 120V 15/1	39	120		Halogen Spot 10°	1100	1.0	6300	530	2900	100	\$4.70
42896-0	39PAR30S/EVP/FL25 120V 15/1	39	120		Halogen Flood 25°	1100	1.0	2000	530	2900	100	\$4.70
42888-8	53PAR30S/EVP/SP10 120V 15/1	53	120		Halogen Spot 10°	1100	1.0	10000	920	2900	100	\$6.38
42890-4	53PAR30S/EVP/FL25 120V 15/1	53	120		Halogen Flood 25°	1100	1.0	3500	920	2900	100	\$6.38
42898-6	53PAR30S/EVP/WFL40 120V 15/1	53	120		Halogen Wide Flood 40°	1100	1.0	1400	920	2900	100	\$6.38
<b>EcoVantage PAR38 Lamps</b>												
42886-2	39PAR38/EVP/SP10 120V 12/1	39	120		Halogen Spot 10°	1100	1.0	7000	570	2900	100	\$4.70
42884-7	39PAR38/EVP/FL25 120V 12/1	39	120		Halogen Flood 25°	1100	1.0	2100	570	2900	100	\$4.70
42889-6	53PAR38/EVP/SP10 120V 12/1	53	120		Halogen Spot 10°	1100	1.0	11000	920	2900	100	\$6.38
42885-4	53PAR38/EVP/FL25 120V 12/1	53	120		Halogen Flood 25°	1100	1.0	3250	920	2900	100	\$6.38
42894-6	72PAR38/EVP/SP10 120V 12/1	72	120		Halogen Spot 10°	1100	1.0	16000	1350	2900	100	\$8.67
42893-8	72PAR38/EVP/FL25 120V 12/1	72	120		Halogen Flood 25°	1100	1.0	4700	1350	2900	100	\$8.67

- 1) Rated average life is the length of operation (in hours) at which point an average of 50% of the lamps will still be operational and 50% will not.
- 2) Based on 3 hrs/day
- 3) Maximum Beam Candlepower.
- 4) Based on 3 hrs/day at a cost of \$0.11 per kWh. Your actual cost may vary depending on use and energy costs in your geographic location.

## Shipping Data (Subject to change without notice)

Product Number	SKU UPC (0-46677)	Outer Bar Code (5-00-46677)	Case Qty.	Case Weight (lbs.)	Case Cube (cu. ft.)	Pallet Qty.	SKUs Per Layer	Layers High	SKU Dimensions (W x D x H) (In.)	Case Dimensions (W x D x H) (In.)	Pallet Dimensions (W x D x H) (In.)
<b>EcoVantage PAR20 Lamps</b>											
42512-4	42512-8	42512-3	15	4	0.24	2970	270	11	2.44 x 3.50 x 0.27	13.00 x 8.00 x 4.00	46.88 x 38.44 x 46.75
42520-7	42520-3	42520-8	15	4	0.24	2970	270	11	2.44 x 3.50 x 0.27	13.00 x 8.00 x 4.00	46.88 x 38.44 x 46.75
<b>EcoVantage PAR30 Long Lamps</b>											
42887-0	42886-0	42886-5	15	8	0.629	1215	135	9	3.5 x 3.5 x 4.75	18.06 x 10.94 x 5.5	47.06 x 39.94 x 49.50
42892-0	42520-3	42520-8	15	8	0.629	1215	135	9	3.5 x 3.5 x 4.75	18.06 x 10.94 x 5.5	47.06 x 39.94 x 49.50
42895-2	42896-9	42896-4	15	8	0.629	1215	135	9	3.5 x 3.5 x 4.75	18.06 x 10.94 x 5.5	47.06 x 39.94 x 49.50
<b>EcoVantage PAR30 Short Lamps</b>											
42891-2	42887-7	42887-2	15	8	0.52	1485	135	11	3.38 x 3.38 x 4	10.81 x 17.69 x 4.69	46.19 x 39.31 x 51.21
42896-0	42884-6	42884-1	15	8	0.52	1485	135	11	3.38 x 3.38 x 4	10.81 x 17.69 x 4.69	46.19 x 39.31 x 51.21
42888-8	42888-4	42888-9	15	8	0.52	1485	135	11	3.38 x 3.38 x 4	10.81 x 17.69 x 4.69	46.19 x 39.31 x 51.21
42890-4	42889-1	42889-6	15	8	0.52	1485	135	11	3.38 x 3.38 x 4	10.81 x 17.69 x 4.69	46.19 x 39.31 x 51.21
42898-6	42890-7	42890-2	15	8	0.52	1485	135	11	3.38 x 3.38 x 4	10.81 x 17.69 x 4.69	46.19 x 39.31 x 51.21
<b>EcoVantage PAR38 Lamps</b>											
42886-2	42892-1	42892-6	12	10.6	0.85	720	180	4	4.31 x 4.31 x 5.44	9.06 x 13.56 x 11.88	45.30 x 40.68 x 47.52
42884-7	42885-3	42885-8	12	10.6	0.85	720	180	4	4.31 x 4.31 x 5.44	9.06 x 13.56 x 11.88	45.30 x 40.68 x 47.52
42889-6	42898-3	42898-8	12	10.6	0.85	720	180	4	4.31 x 4.31 x 5.44	9.06 x 13.56 x 11.88	45.30 x 40.68 x 47.52
42885-4	42895-2	42895-7	12	10.6	0.85	720	180	4	4.31 x 4.31 x 5.44	9.06 x 13.56 x 11.88	45.30 x 40.68 x 47.52
42894-6	42894-5	42894-0	12	10.6	0.85	720	180	4	4.31 x 4.31 x 5.44	9.06 x 13.56 x 11.88	45.30 x 40.68 x 47.52
42893-8	42893-8	42893-3	12	10.6	0.85	720	180	4	4.31 x 4.31 x 5.44	9.06 x 13.56 x 11.88	45.30 x 40.68 x 47.52



© 2012 Philips Lighting Company, A Division of Philips Electronics North America Corporation. All rights reserved. Printed in USA 10/12 P-6463 www.philips.com

Philips Lighting Company  
200 Franklin Square Drive  
Somerset, NJ 08873  
1-800-555-0050

Philips Lighting  
281 Hillmount Road  
Markham, Ontario  
Canada L6C 2S3  
1-800-555-0050  
A Division of Philips Electronics Ltd.