



T8 Standard

F32T8/TL735 ALTO

Philips T8 lamps are energy-efficient lighting solutions.

Product data

• General Characteristics

Base	Medium Bi-Pin [Medium Bi-Pin Fluorescent]
Base Information	Green Base
Bulb	T8
Energy Saving	Energy Saving
Rated Avg Life [12-Hr Prog St]	36000 hr
Rated Avg Life [12-Hr Inst St]	30000 hr
Rated Avg Life [3-Hr Prog St]	30000 hr
Rated Avg Life [3-Hr Inst St]	24000 hr

• Light Technical Characteristics

Color Code	TL735 [CCT of 3500K]
Color Rendering Index	78 Ra8
Color Designation	TL735
Color Temperature	3500 K
Initial lumen	2600 Lm
Design Mean Lumens	2470 Lm

• Electrical Characteristics

Watts	32 W
-------	------

• Environmental Characteristics

Mercury (Hg) Content	1.7 mg
Picogram per Lumen Hour	27 p/LuHr

• Product Dimensions

Nominal Length [inch]	48
-----------------------	----

• Footnotes

Footnotes Fluorescent/CFL	920 [Circle E- The encircled E means this bulb meets Federal minimum efficiency standards.]
---------------------------	---


• Product Data

Product number	281618
Full product name	F32T8/TL735 ALTO
Short product name	F32T8/TL735 ALTO 30PK
Pieces per Sku	1
eop_pck_cfg	30
Skus/Case	30
Bar code on pack	46677281618
Bar code on case	50046677281613
Logistics code(s)	927869773512
eop_net_weight_pp	0.001 kg


PHILIPS

sense and simplicity


Dimensional drawing



G13, T8



G13



G13, T8



© 2012 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2012, August 4
data subject to change