



Energy Saver GU24

13W GU24 EL/mDT

Looking for an energy saver that does not look like one? The Philips EnergySaver family provides energy efficient lighting options that don't just provide similar light as your standard incandescent light bulb, they also have the same classic shapes. Try the Philips EnergySavers and see how they truly provide advanced lighting designed around your needs.

Product data

• General Characteristics

Base	GU24
Bulb	EL/mDT
RatedAvgLife(See Family Notes)	10000 hr
Rated Lifetime (hours)	10000 hr
Rated Lifetime (years)	10 an

• Light Technical Characteristics

Color Code	827 [CCT of 2700K]
Color Rendering Index	80 (min) Ra8
Color Designation	Warm White
Color Temperature	2700 K
Initial lumen	900 Lm
Luminous Efficacy Lamp	65 Lm/W
Lumen Maintenance 2000h	85 %
Lumen Maintenance 5000h	75 %
Chromaticity Coordinate X	459 -
Chromaticity Coordinate Y	412 -

• Electrical Characteristics

Watts	13 W
Power Factor	0.55 -
Voltage	110-127 V
Lamp Current mA	190 mA
Line Frequency	50/60 Hz
Starting Time	0.2 s
Warm-up Time to 60% Light Outp	60 (max) s

• Product Dimensions

Overall Length C	95.0 (max) mm
Diameter D	52.0 (max) mm
Width F	38.5 (max) mm

• Product Data


Product number	417238
Full product name	13W GU24 EL/mDT
Short product name	EL/mdT 13W GU24 2700K
Pieces per Sku	1
eop_pck_cfg	6
Skus/Case	6
Bar code on pack	46677417239
Bar code on case	50046677417234
Logistics code(s)	929689420201
eop_net_weight_pp	0.060 kg

Dimensional drawing

PHILIPS

sense and simplicity

Dimensional drawing



13W, GU24

Product	C (Max)	D (Max)	F (Max)
TORNADO 13W/827 GU24 110-127V 50/60Hz	95.0	52.0	38.5



© 2012 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2012, November 2
data subject to change