

Philips LED Lamps Dimmer Compatibility Lists

Revised: 01/15/2013

PHILIPS



Philips LED Lamps
3W/Candle

Applicable Part Numbers
410209, 410217, 420414, 420422, 420430, 426916, 427237

Brand	Model	Part #	Lamp Quantity		
			Best	OK	NR
Cooper	REACT	RI061-VW-K2			X
Leviton	Decora	6161			X
Leviton	SureSlide	6613			X
Leviton	SureSlide	6615P			X
Leviton	SureSlide	6631			X
Leviton	SureSlide	6633P			
Leviton	SureSlide	6674	1-6	7-10	>10
Leviton	Trimatron	6681			X
Leviton	Trimatron	6683			X
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ		1-12	
Leviton	IllumaTech	IPI06			X
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			X
Lightolier	Vega	V600VAU	1-2	3-12	
Lightolier	Vega	V1000VAU			
Lightolier	Sunrise	ZP600VA			X
Lightolier	Sunrise	ZP600			X
Lightolier	Vega	V600			X
Lightolier	Onset	OS600			
Lightolier	Onset	OS600VA		1-4	>4
Lightolier	Onset	OS1000VA		1-4	>4
Lightolier	Astral Slider	A600			X
Lightolier	Astral Slider	AP600			X
Lightolier	MultiSet	MHP600VA	1-12		
Lightolier	Momentum	MP2000VAI	1-16		
WattStopper	Micro Decorator	DCD267-W	1-12		
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W			X
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W			X
WattStopper	Slide	SD-603-W	1-12		

Brand	Model	Part #	Lamp Quantity		
			Best	OK	NR
Lutron	Skylark	CTCL-153P			X
Lutron	Diva	DVCL-153PD			X
Lutron	Diva	DVCL-153P v2		1-12	
Lutron	Diva	DVPDC-203			X
Lutron	Diva	DV-600P	1-8		
Lutron	Diva	DV-603PG			X
Lutron	DIVA	DVELV-300P		1-2	>2
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P			X
Lutron	Maestro	MACL-153M v2		1-12	
Lutron	Maestro	MAELV-600	1-12		
Lutron	Maestro	MALV-600			X
Lutron	Maestro	MRF2-600M	1-12		
Lutron	Maestro	MRF2-6ND-120			X
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600	1-12		
Lutron	Nova	NLV1000	1-20		
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P	1-30		
Lutron	Qoto	Q-600P			X
Lutron	RADIO RA	RRD-6NA	1-12		
Lutron	Skylark	S-600P			X
Lutron	Skylark	SELV-300P		1-12	
Lutron	Skylark	SLV-600P	1-12		
Lutron	Toggler	TG-600P			X
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX	1-30		
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker, good dimming range. Possible minor pop-on.
OK	A minor, low % flicker which is hard to find, some limit of dim-range, relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Notes
Lamp load is limited to 25% of dimmer's incandescent rating unless higher value approved by dimmer manufacturer.
* - Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.
Latest Update 01/15/2013





Philips LED Lamps
7W/PAR20

Applicable Part Numbers
410084, 410092, 410100, 417873, 418574, 418582

Brand	Model	Part #	Lamp Quantity		
			Best	OK	NR
Cooper	REACT	RI061-VW-K2			
Leviton	Decora	6161			X
Leviton	SureSlide	6613			X
Leviton	SureSlide	6615P			X
Leviton	SureSlide	6631	3-16	1-2	
Leviton	SureSlide	6633P			
Leviton	SureSlide	6674	1-16		
Leviton	Trimatron	6681	1-4		>4
Leviton	Trimatron	6683		1-4	>4
Leviton	Trimatron	6684			
Leviton	IlumaTech	IPE04-1LZ			X
Leviton	IlumaTech	IPI06			X
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			X
Lightolier	Vega	V600VAU	1-16		
Lightolier	Vega	V1000VAU			
Lightolier	Sunrise	ZP600VA	1-16		
Lightolier	Sunrise	ZP600			X
Lightolier	Vega	V600			
Lightolier	Onset	OS600			X
Lightolier	Onset	OS600VA		1-16	
Lightolier	Onset	OS1000VA			X
Lightolier	Astral Slider	A600			X
Lightolier	Astral Slider	AP600			X
Lightolier	MultiSet	MHP600VA	1-16		
Lightolier	Momentum	MP2000VAI	1-16		
WattStopper	Micro Decorator	DCD267-W	1-16		
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W	1-6		>6
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W			X
WattStopper	Slide	SD-603-W	1-10	11-12	>12

Brand	Model	Part #	Lamp Quantity		
			Best	OK	NR
Lutron	Skylark	CTCL-153P			X
Lutron	Diva	DVCL-153PD			X
Lutron	Diva	DVCL-153P v2	1-16		
Lutron	Diva	DVPDC-203		1-12	
Lutron	Diva	DV-600P	1-16		
Lutron	Diva	DV-603PG			X
Lutron	DIVA	DVELV-300P	3-10		1 or 2
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P			X
Lutron	Maestro	MACL-153M v2			X
Lutron	Maestro	MAELV-600			X
Lutron	Maestro	MALV-600			X
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120		1-16	
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600	1-16		
Lutron	Nova	NLV1000	1-16		
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P	1-16		
Lutron	Qoto	Q-600P			X
Lutron	RADIO RA	RRD-6NA		1-16	
Lutron	Skylark	S-600P			X
Lutron	Skylark	SELV-300P			X
Lutron	Skylark	SLV-600P			X
Lutron	Toggler	TG-600P			X
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker, good dimming range. Possible minor pop-on.
OK	A minor, low % flicker which is hard to find, some limit of dim-range, relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Notes
Lamp load is limited to 25% of dimmer's incandescent rating unless higher value approved by dimmer manufacturer.
* - Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.
Latest Update 01/15/2013





**Philips LED Lamps
8W/A19 Bulb**

Applicable Part Numbers
409938

Brand	Model	Part #	Lamp Quantity		
			Best	OK	NR
Cooper	REACT	RI061-VW-K2	1-16		
Leviton	Decora	6161			X
Leviton	SureSlide	6613			X
Leviton	SureSlide	6615P			X
Leviton	SureSlide	6631			X
Leviton	SureSlide	6633P			
Leviton	SureSlide	6674	1-14		
Leviton	Trimatron	6681			X
Leviton	Trimatron	6683			X
Leviton	Trimatron	6684			X
Leviton	IllumaTech	IPE04-1LZ		1-16	
Leviton	IllumaTech	IPI06		1-16	
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			X
Lightolier	Vega	V600VAU	1-2	3-16	
Lightolier	Vega	V1000VAU			
Lightolier	Sunrise	ZP600VA			X
Lightolier	Sunrise	ZP600			X
Lightolier	Vega	V600			X
Lightolier	Onset	OS600	3-16		1 or 2
Lightolier	Onset	OS600VA	1-4		>4
Lightolier	Onset	OS1000VA	1-4		>4
Lightolier	Astral Slider	A600			X
Lightolier	Astral Slider	AP600			X
Lightolier	MultiSet	MHP600VA	1-8	9-16	
Lightolier	Momentum	MP2000VAI	1-16		
WattStopper	Micro Decorator	DCD267-W	1-16		
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W			
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W			
WattStopper	Slide	SD-603-W			

Brand	Model	Part #	Lamp Quantity		
			Best	OK	NR
Lutron	Skylark	CTCL-153P	1-4		
Lutron	Diva	DVCL-153PD		1-12	
Lutron	Diva	DVCL-153P v2	1-16		
Lutron	Diva	DVPCD-203		1-4	
Lutron	Diva	DV-600P	1-16		
Lutron	Diva	DV-603PG			X
Lutron	DIVA	DVELV-300P	1-9		
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P			X
Lutron	Maestro	MACL-153M v2			X
Lutron	Maestro	MAELV-600	1-16		
Lutron	Maestro	MALV-600			X
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120			X
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600	1-16		
Lutron	Nova	NLV1000	1-16*		
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P			X
Lutron	Qoto	Q-600P			X
Lutron	RADIO RA	RRD-6NA	1-16		
Lutron	Skylark	S-600P			
Lutron	Skylark	SELV-300P			
Lutron	Skylark	SLV-600P	1-16		
Lutron	Toggler	TG-600P			
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX	1-32		
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker, good dimming range. Possible minor pop-on.
OK	A minor, low % flicker which is hard to find, some limit of dim-range, relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity fo lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Notes
Lamp load is limited to 25% of dimmer's incandescent rating unless higher value approved by dimmer manufacturer.
* - Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.
Latest Update 01/15/2013





**Philips LED Lamps
8W/A19 Bulb**

Applicable Part Numbers
417048, 414839

Brand	Model	Part #	Lamp Quantity		
			Best	OK	NR
Cooper	REACT	RI061-VW-K2		1-4	>4
Leviton	Decora	6161			
Leviton	SureSlide	6613			X
Leviton	SureSlide	6615P			X
Leviton	SureSlide	6631			
Leviton	SureSlide	6633P			
Leviton	SureSlide	6674		1-7	
Leviton	Trimatron	6681	1-4	5-6	>6
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ			
Leviton	IllumaTech	IPI06			X
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Lightolier	Vega	V600VAU	1-8		
Lightolier	Vega	V1000VAU			
Lightolier	Sunrise	ZP600VA	1-8		
Lightolier	Sunrise	ZP600			
Lightolier	Vega	V600			
Lightolier	Onset	OS600			
Lightolier	Onset	OS600VA			X
Lightolier	Onset	OS1000VA			
Lightolier	Astral Slider	A600			
Lightolier	Astral Slider	AP600			
Lightolier	MultiSet	MHP600VA		1-16	
Lightolier	Momentum	MP2000VAI	1-7		
WattStopper	Micro Decorator	DCD267-W			X
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W			
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W			
WattStopper	Slide	SD-603-W			

Brand	Model	Part #	Lamp Quantity		
			Best	OK	NR
Lutron	Skylark	CTCL-153P			
Lutron	Diva	DVCL-153PD	1-8		
Lutron	Diva	DVCL-153P v2		1-8	
Lutron	Diva	DVPDC-203			
Lutron	Diva	DV-600P			X
Lutron	Diva	DV-603PG			X
Lutron	DIVA	DVELV-300P	1-18		
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P			X
Lutron	Maestro	MACL-153M v2			X
Lutron	Maestro	MAELV-600			
Lutron	Maestro	MALV-600			
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120			X
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600	1-18		
Lutron	Nova	NLV1000	1-24*		
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P			X
Lutron	Qoto	Q-600P			X
Lutron	RADIO RA	RRD-6NA		1-16	
Lutron	Skylark	S-600P			X
Lutron	Skylark	SELV-300P			
Lutron	Skylark	SLV-600P			X
Lutron	Toggler	TG-600P			
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker, good dimming range. Possible minor pop-on.
OK	A minor, low % flicker which is hard to find, some limit of dim-range, relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Notes
Lamp load is limited to 25% of dimmer's incandescent rating unless higher value approved by dimmer manufacturer.
* - Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.
Latest Update 01/15/2013





Philips LED Lamps
10W/A19 Bulb
L Prize® Award Winning LED Bulb

Applicable Part Numbers
420224, 420075

Brand	Model	Part #	Lamp Quantity		
			Best	OK	NR
Cooper	REACT	RI061-VW-K2			X
Leviton	Decora	6161	1-4		
Leviton	SureSlide	6613		1-5	>5
Leviton	SureSlide	6615P		1-4	>4
Leviton	SureSlide	6631			
Leviton	SureSlide	6633P			
Leviton	SureSlide	6674	1	2	>2
Leviton	Trimatron	6681			X
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ			
Leviton	IllumaTech	IPI06	1-2		>2
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Lightolier	Vega	V600VAU		1-4	
Lightolier	Vega	V1000VAU			
Lightolier	Sunrise	ZP600VA	1-10*		
Lightolier	Sunrise	ZP600			
Lightolier	Vega	V600			
Lightolier	Onset	OS600			
Lightolier	Onset	OS600VA	1-4	5-6	>6
Lightolier	Onset	OS1000VA			
Lightolier	Astral Slider	A600			
Lightolier	Astral Slider	AP600			
Lightolier	MultiSet	MHP600VAI	1-9*		
Lightolier	Momentum	MP2000VAI	3-8	1-2	
WattStopper	Micro Decorator	DCD267-W		1-11*	
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W			
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W			
WattStopper	Slide	SD-603-W			

Brand	Model	Part #	Lamp Quantity		
			Best	OK	NR
Lutron	Skylark	CTCL-153P			X
Lutron	Diva	DVCL-153PD		1	>1
Lutron	Diva	DVCL-153P v2	1-9*		
Lutron	Diva	DVPDC-203			
Lutron	Diva	DV-600P	1-4	5	>5
Lutron	Diva	DV-603PG	1-4	5	>5
Lutron	DIVA	DVELV-300P	1-5		
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P	1-4		
Lutron	Maestro	MACL-153M v2	1-9*		
Lutron	Maestro	MAELV-600		1-4	
Lutron	Maestro	MALV-600			X
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120		1-11*	
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600	1-10*		
Lutron	Nova	NLV1000	1-10*		
Lutron	Nova	NT-600-W	1-8		
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300	1-4		
Lutron	Grafik Eye	QSGR-3P	1-9*		
Lutron	Qoto	Q-600P	1-8		>8
Lutron	RADIO RA	RRD-6NA	1-9*		
Lutron	Skylark	S-600P			>4
Lutron	Skylark	SELV-300P			
Lutron	Skylark	SLV-600P		1-4	>4
Lutron	Toggle	TG-600P			>6
Lutron	Credenza	TT-300		1-2	
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX	1-8		
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I	1-8		

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker, good dimming range. Possible minor pop-on.
OK	A minor, low % flicker which is hard to find, some limit of dim-range, relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity fo lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Notes
Lamp load is limited to 25% of dimmer's incandescent rating unless higher value approved by dimmer manufacturer.
* - Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.
Latest Update 01/15/2013





**Philips LED Lamps
11W/A19 Bulb**

Applicable Part Numbers
423491, 424382, 429258, 425264

Brand	Model	Part #	Lamp Quantity		
			Best	OK	NR
Cooper	REACT	RI061-VW-K2	1-2		>3
Leviton	Decora	6161			
Leviton	SureSlide	6613	1-13		
Leviton	SureSlide	6615P	1-2	3-4	>4
Leviton	SureSlide	6631			
Leviton	SureSlide	6633P			
Leviton	SureSlide	6674	1-3	4	>4
Leviton	Trimatron	6681			X
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ			
Leviton	IllumaTech	IPI06			X
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Leviton	Vega	V600VAU	1-13		
Lightolier	Vega	V1000VAU	1-11*		
Lightolier	Sunrise	ZP600VA		1-2	>2
Lightolier	Sunrise	ZP600			
Lightolier	Vega	V600			
Lightolier	Onset	OS600			
Lightolier	Onset	OS600VA	1-13		
Lightolier	Onset	OS1000VA			
Lightolier	Astral Slider	A600			
Lightolier	Astral Slider	AP600			
Lightolier	MultiSet	MHP600VA	1-2		>2
Lightolier	Momentum	MP2000VAI			
WattStopper	Micro Decorator	DCD267-W	1-13		
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W	1-12		
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W	1-8		>8
WattStopper	Slide	SD-603-W	1-8		>8

Brand	Model	Part #	Lamp Quantity		
			Best	OK	NR
Lutron	Skylark	CTCL-153P	1-4	5	>5
Lutron	Divi	DVCL-153PD		1-13	
Lutron	Divi	DVCL-153P v2	1-13		
Lutron	Divi	DVPDC-203			
Lutron	Divi	DV-600P		1-4	>4
Lutron	Divi	DV-603PG			
Lutron	DIVA	DVELV-300P	1-13		
Lutron	Divi	DVWCL-153PDH			
Lutron	Glyder	GL-600P			
Lutron	Maestro	MAELV-153M v2	1-13		
Lutron	Maestro	MAELV-600			
Lutron	Maestro	MALV-600			
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120	1-13		
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600		1-13	
Lutron	Nova	NLV1000		1-13*	
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P	1-13*		
Lutron	Qoto	Q-600P			
Lutron	RADIO RA	RRD-6NA	1-13		
Lutron	Skylark	S-600P			
Lutron	Skylark	SELV-300P			
Lutron	Skylark	SLV-600P		1-13	
Lutron	Toggle	TG-600P			
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker, good dimming range. Possible minor pop-on.
OK	A minor, low % flicker which is hard to find, some limit of dim-range, relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Notes
Lamp load is limited to 25% of dimmer's incandescent rating unless higher value approved by dimmer manufacturer.
* - Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.
Latest Update 01/15/2013





Philips LED Lamps
12W/PAR30L and PAR30S
13W/PAR30S

Applicable Part Numbers
410118, 410126, 410167, 414482, 414490, 414573, 414581, 414599, 423442, 423459

Brand	Model	Part #	Lamp Quantity		
			Best	OK	NR
Cooper	REACT	RI061-VW-K2		1-4	>4
Leviton	Decora	6161			X
Leviton	SureSlide	6613	1-8		
Leviton	SureSlide	6615P		1-12	
Leviton	SureSlide	6631	1-8		
Leviton	SureSlide	6633P			
Leviton	SureSlide	6674		1-12	
Leviton	Trimatron	6681	1-3		
Leviton	Trimatron	6683	1-3		
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ	1-8		
Leviton	IllumaTech	IPI06		1-4	>4
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			X
Lightolier	Vega	V600VAU		1-12	
Lightolier	Vega	V1000VAU			
Lightolier	Sunrise	ZP600VA		1-12	
Lightolier	Sunrise	ZP600			X
Lightolier	Vega	V600	1-4		
Lightolier	Onset	OS600			X
Lightolier	Onset	OS600VA		1-8	>8
Lightolier	Onset	OS1000VA		1-8	>8
Lightolier	Astral Slider	A600	1-8		>8
Lightolier	Astral Slider	AP600			X
Lightolier	MultiSet	MHP600VA	1-12		
Lightolier	Momentum	MP2000VAI	1-5*		
WattStopper	Micro Decorator	DCD267-W		1-12	
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W			
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W			
WattStopper	Slide	SD-603-W			

Brand	Model	Part #	Lamp Quantity		
			Best	OK	NR
Lutron	Skylark	CTCL-153P		1-2	
Lutron	Diva	DVCL-153PD			X
Lutron	Diva	DVCL-153P v2	1-12		
Lutron	Diva	DVPDC-203			X
Lutron	Diva	DV-600P	1-12		
Lutron	Diva	DV-603PG	1-12		
Lutron	DIVA	DVELV-300P	1-6		
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P		1-8	>8
Lutron	Maestro	MACL-153M v2	1-12		
Lutron	Maestro	MAELV-600	1-12		
Lutron	Maestro	MALV-600			X
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120			X
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600	1-12		
Lutron	Nova	NLV1000	1-16		
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P		1-12	
Lutron	Qoto	Q-600P		1-8	>8
Lutron	RADIO RA	RRD-6NA	1-12		
Lutron	Skylark	S-600P			>8
Lutron	Skylark	SELV-300P			>6
Lutron	Skylark	SLV-600P		1-12	
Lutron	Toggler	TG-600P		1-6	>6
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker, good dimming range. Possible minor pop-on.
OK	A minor, low % flicker which is hard to find, some limit of dim-range, relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Notes
Lamp load is limited to 25% of dimmer's incandescent rating unless higher value approved by dimmer manufacturer.
* - Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.
Latest Update 01/15/2013





Philips LED Lamps
12.5W/A19

Applicable Part Numbers
409946 (12E26A60 model only)

Brand	Model	Part #	Lamp Quantity		
			Best	OK	NR
Cooper	REACT	RI061-VW-K2	1-12		
Leviton	Decora	6161	1-12		
Leviton	SureSlide	6613	1-12		
Leviton	SureSlide	6615P	1-12		
Leviton	SureSlide	6631	1-12		
Leviton	SureSlide	6633P			
Leviton	SureSlide	6674	1-12		
Leviton	Trimatron	6681	1-8		
Leviton	Trimatron	6683	1-8		
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ	1-12		
Leviton	IllumaTech	IPI06		1-4	>4
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			X
Lightolier	Vega	V600VAU	1-12		
Lightolier	Vega	V1000VAU			
Lightolier	Sunrise	ZP600VA	1-12		
Lightolier	Sunrise	ZP600	1-4		>4
Lightolier	Vega	V600	1-12		
Lightolier	Onset	OS600			X
Lightolier	Onset	OS600VA			
Lightolier	Onset	OS1000VA	1-8		>8
Lightolier	Astral Slider	A600		1-8	>8
Lightolier	Astral Slider	AP600		1-12	
Lightolier	MultiSet	MHP600VA	1-7	8-12	
Lightolier	Momentum	MP2000VAI	1-16		
WattStopper	Micro Decorator	DCD267-W		1-12	
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W		1-8	>8
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W	1-12		
WattStopper	Slide	SD-603-W	1-12		

Brand	Model	Part #	Lamp Quantity		
			Best	OK	NR
Lutron	Skylark	CTCL-153P	1-12		
Lutron	Diva	DVCL-153PD	1-12		
Lutron	Diva	DVCL-153P v2	1-6	7-8	
Lutron	Diva	DVPDC-203		1-6	
Lutron	Diva	DV-600P		1-8	>8
Lutron	Diva	DV-603PG	1-12		
Lutron	DIVA	DVELV-300P	1-12		
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P	1-12		
Lutron	Maestro	MACL-153M v2	1-5	6-8	>8
Lutron	Maestro	MAELV-600	1-12		
Lutron	Maestro	MALV-600			X
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120	1-12		
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600	1-12		
Lutron	Nova	NLV1000	1-12*		
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P	1-13*		
Lutron	Qoto	Q-600P		1-12	
Lutron	RADIO RA	RRD-6NA	1-12		
Lutron	Skylark	S-600P		1-12	
Lutron	Skylark	SELV-300P	1-12		
Lutron	Skylark	SLV-600P	1-12		
Lutron	Toggle	TG-600P	1-12		
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker, good dimming range. Possible minor pop-on.
OK	A minor, low % flicker which is hard to find, some limit of dim-range, relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Notes
Lamp load is limited to 25% of dimmer's incandescent rating unless higher value approved by dimmer manufacturer.
* - Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.
Latest Update 01/15/2013





Philips LED Lamps
12.5W/A19

Applicable Part Numbers
409946 (12E26A60-1 and 9290001829 models only)

Brand	Model	Part #	Lamp Quantity		
			Best	OK	NR
Cooper	REACT	RI061-VW-K2			
Leviton	Decora	6161			
Leviton	SureSlide	6613	1-12		
Leviton	SureSlide	6615P	1-12		
Leviton	SureSlide	6631			
Leviton	SureSlide	6633P			
Leviton	SureSlide	6674	1-12		
Leviton	Trimatron	6681		1-8	>8
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ			
Leviton	IllumaTech	IPI06	1-12		
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Lightolier	Vega	V600VAU	1-12		
Lightolier	Vega	V1000VAU			
Lightolier	Sunrise	ZP600VA	1-12		
Lightolier	Sunrise	ZP600			
Lightolier	Vega	V600			
Lightolier	Onset	OS600			
Lightolier	Onset	OS600VA	1-12		
Lightolier	Onset	OS1000VA			
Lightolier	Astral Slider	A600			
Lightolier	Astral Slider	AP600			
Lightolier	MultiSet	MHP600VA	1-12		
Lightolier	Momentum	MP2000VAI			
WattStopper	Micro Decorator	DCD267-W	1-12		
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W		1-14	
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W	1-12		
WattStopper	Slide	SD-603-W	1-12		

Brand	Model	Part #	Lamp Quantity		
			Best	OK	NR
Lutron	Skylark	CTCL-153P			
Lutron	Diva	DVCL-153PD			
Lutron	Diva	DVCL-153P v2	1-12		
Lutron	Diva	DVPDC-203			
Lutron	Diva	DV-600P	1-8	9-12	
Lutron	Diva	DV-603PG			
Lutron	DIVA	DVELV-300P	1-12		
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P			
Lutron	Maestro	MACL-153M v2	1-12		
Lutron	Maestro	MAELV-600			
Lutron	Maestro	MALV-600			
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120	1-12		
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600	1-12		
Lutron	Nova	NLV1000	1-16*		
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P	1-12*		
Lutron	Qoto	Q-600P			
Lutron	RADIO RA	RRD-6NA	1-12		
Lutron	Skylark	S-600P			
Lutron	Skylark	SELV-300P			
Lutron	Skylark	SLV-600P			X
Lutron	Toggler	TG-600P			
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker, good dimming range. Possible minor pop-on.
OK	A minor, low % flicker which is hard to find, some limit of dim-range, relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Notes
Lamp load is limited to 25% of dimmer's incandescent rating unless higher value approved by dimmer manufacturer.
* - Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.
Latest Update 01/15/2013





Philips LED Lamps
13W/BR30 (AirFlux)

Applicable Part Numbers
420554, 420273, 421941, 423798

Brand	Model	Part #	Lamp Quantity		
			Best	OK	NR
Cooper	REACT	RI061-VW-K2			
Leviton	Decora	6161			
Leviton	SureSlide	6613	1-11		
Leviton	SureSlide	6615P	1-11		
Leviton	SureSlide	6631			
Leviton	SureSlide	6633P			
Leviton	SureSlide	6674	1-11		
Leviton	Trimatron	6681		1-8	>8
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ			
Leviton	IllumaTech	IPI06	1-11		
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Lightolier	Vega	V600VAU	1-11		
Lightolier	Vega	V1000VAU	1-16*		
Lightolier	Sunrise	ZP600VA	1-11		
Lightolier	Sunrise	ZP600		1-5	>5
Lightolier	Vega	V600			
Lightolier	Onset	OS600			X
Lightolier	Onset	OS600VA	1-11		
Lightolier	Onset	OS1000VA			
Lightolier	Astral Slider	A600			
Lightolier	Astral Slider	AP600		1-7	>7
Lightolier	MultiSet	MHP600VA	1-11		
Lightolier	Momentum	MP2000VAI			
WattStopper	Micro Decorator	DCD267-W	1-11		
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W			
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W			
WattStopper	Slide	SD-603-W			

Brand	Model	Part #	Lamp Quantity		
			Best	OK	NR
Lutron	Skylark	CTCL-153P	1-11		
Lutron	Diva	DVCL-153PD		1-11	
Lutron	Diva	DVCL-153P v2	1-11		
Lutron	Diva	DVPDC-203			
Lutron	Diva	DV-600P		1-11	
Lutron	Diva	DV-603PG			
Lutron	DIVA	DVELV-300P	1-11		
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P			
Lutron	Maestro	MACL-153M v2	1-11		
Lutron	Maestro	MAELV-600			
Lutron	Maestro	MALV-600	1-11		
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120		1-11	
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600	1-11		
Lutron	Nova	NLV1000	1-16*		
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P	1-11*		
Lutron	Qoto	Q-600P			
Lutron	RADIO RA	RRD-6NA	1-11		
Lutron	Skylark	S-600P			
Lutron	Skylark	SELV-300P			
Lutron	Skylark	SLV-600P	1-11		
Lutron	Toggle	TG-600P			
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker, good dimming range. Possible minor pop-on.
OK	A minor, low % flicker which is hard to find, some limit of dim-range, relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Notes
Lamp load is limited to 25% of dimmer's incandescent rating unless higher value approved by dimmer manufacturer.
* - Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.
Latest Update 01/15/2013





Philips LED Lamps
13W/BR30 DimTone
(AirFlux)

Applicable Part Numbers
426445

Brand	Model	Part #	Lamp Quantity		
			Best	OK	NR
Cooper	REACT	RI061-VW-K2	1-11		
Leviton	Decora	6161			
Leviton	SureSlide	6613	1-11		
Leviton	SureSlide	6615P	1-6		
Leviton	SureSlide	6631			
Leviton	SureSlide	6633P			
Leviton	SureSlide	6674	1-4		>4
Leviton	Trimatron	6681	1-4		>4
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ	1-8		
Leviton	IllumaTech	IPI06	1-7		>7
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Lightolier	Vega	V600VAU	1-11		
Lightolier	Vega	V1000VAU	1-16*		
Lightolier	Sunrise	ZP600VA	1-4	5	>5
Lightolier	Sunrise	ZP600			X
Lightolier	Vega	V600			
Lightolier	Onset	OS600			X
Lightolier	Onset	OS600VA	1-11		
Lightolier	Onset	OS1000VA			
Lightolier	Astral Slider	A600			
Lightolier	Astral Slider	AP600	1-11		
Lightolier	MultiSet	MHP600VA	1-6		>6
Lightolier	Momentum	MP2000VAI			
WattStopper	Micro Decorator	DCD267-W	1-11		
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W			
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W			
WattStopper	Slide	SD-603-W			

Brand	Model	Part #	Lamp Quantity		
			Best	OK	NR
Lutron	Skylark	CTCL-153P			
Lutron	Divi	DVCL-153PD		1-11	
Lutron	Divi	DVCL-153P v2	1-11		
Lutron	Divi	DVPDC-203	1-11		
Lutron	Divi	DV-600P	1-4	5	>5
Lutron	Divi	DV-603PG			
Lutron	DIVA	DVELV-300P	1-6		
Lutron	Divi	DVWCL-153PDH			
Lutron	Glyder	GL-600P			
Lutron	Maestro	MAELV-600	1-11		
Lutron	Maestro	MAELV-600	1-11		
Lutron	Maestro	MALV-600			
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120	1-11		
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600	1-11		
Lutron	Nova	NLV1000	1-16*		
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300	1-6		
Lutron	Grafik Eye	QSGR-3P	1-13*		
Lutron	Qoto	Q-600P			
Lutron	RADIO RA	RRD-6NA	1-11		
Lutron	Skylark	S-600P			
Lutron	Skylark	SELV-300P			
Lutron	Skylark	SLV-600P	1-11		
Lutron	Toggler	TG-600P			
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker, good dimming range. Possible minor pop-on.
OK	A minor, low % flicker which is hard to find, some limit of dim-range, relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Notes
Lamp load is limited to 25% of dimmer's incandescent rating unless higher value approved by dimmer manufacturer.
* - Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.
Latest Update 01/15/2013





**Philips LED Lamps
13W/PAR30 (AirFlux)**

Applicable Part Numbers
420471, 420497, 420505, 420802, 423467, 423475, 425330, 425348, 425355, 425363, 425371, 425389, 425397

Brand	Model	Part #	Lamp Quantity		
			Best	OK	NR
Cooper	REACT	RI061-VW-K2			X
Leviton	Decora	6161			
Leviton	SureSlide	6613	1-11		
Leviton	SureSlide	6615P	1-11		
Leviton	SureSlide	6631			
Leviton	SureSlide	6633P			
Leviton	SureSlide	6674	1-11		
Leviton	Trimatron	6681			X
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ			
Leviton	IllumaTech	IPI06		1-2	>2
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Lightolier	Vega	V600VAU	1-11		
Lightolier	Vega	V1000VAU			
Lightolier	Sunrise	ZP600VA	1-11		
Lightolier	Sunrise	ZP600			
Lightolier	Vega	V600			
Lightolier	Onset	OS600			
Lightolier	Onset	OS600VA	1-8		>8
Lightolier	Onset	OS1000VA			
Lightolier	Astral Slider	A600			
Lightolier	Astral Slider	AP600			
Lightolier	MultiSet	MHP600VA	1-11		
Lightolier	Momentum	MP2000VAI			
WattStopper	Micro Decorator	DCD267-W	1-11		
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W			
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W			
WattStopper	Slide	SD-603-W			

Brand	Model	Part #	Lamp Quantity		
			Best	OK	NR
Lutron	Skylark	CTCL-153P			
Lutron	Diva	DVCL-153PD		1-11	
Lutron	Diva	DVCL-153P v2	1-11		
Lutron	Diva	DVPDC-203			
Lutron	Diva	DV-600P	1-11		
Lutron	Diva	DV-603PG			
Lutron	DIVA	DVELV-300P	1-11		
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P			
Lutron	Maestro	MACL-153M v2	1-11		
Lutron	Maestro	MAELV-600			
Lutron	Maestro	MALV-600			
Lutron	Maestro	MRF2-600M	1-11		
Lutron	Maestro	MRF2-6ND-120	1-11*		
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600	1-11		
Lutron	Nova	NLV1000	1-16*		
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P	1-11*		
Lutron	Qoto	Q-600P			
Lutron	RADIO RA	RRD-6NA	1-11		
Lutron	Skylark	S-600P			
Lutron	Skylark	SELV-300P			
Lutron	Skylark	SLV-600P	1-11		
Lutron	Toggler	TG-600P			
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker, good dimming range. Possible minor pop-on.
OK	A minor, low % flicker which is hard to find, some limit of dim-range, relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Notes
Lamp load is limited to 25% of dimmer's incandescent rating unless higher value approved by dimmer manufacturer.
* - Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.
Latest Update 01/15/2013





Philips LED Lamps
14.5W/BR40

Applicable Part Numbers
420562, 420299, 423756

Brand	Model	Part #	Lamp Quantity		
			Best	OK	NR
Cooper	REACT	RI061-VW-K2		1-10	
Leviton	Decora	6161			
Leviton	SureSlide	6613	1-10		
Leviton	SureSlide	6615P			NR
Leviton	SureSlide	6631			
Leviton	SureSlide	6633P			
Leviton	SureSlide	6674	1-10		
Leviton	Trimatron	6681	1-10		
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ			
Leviton	IllumaTech	IPI06		1-10	
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Lightolier	Vega	V600VAU	1-10		
Lightolier	Vega	V1000VAU			
Lightolier	Sunrise	ZP600VA	1-10		
Lightolier	Sunrise	ZP600			
Lightolier	Vega	V600			
Lightolier	Onset	OS600			
Lightolier	Onset	OS600VA	1-10		
Lightolier	Onset	OS1000VA			
Lightolier	Astral Slider	A600			
Lightolier	Astral Slider	AP600			
Lightolier	MultiSet	MHP600VA	1-10		
Lightolier	Momentum	MP2000VAI			
WattStopper	Micro Decorator	DCD267-W	1-10		
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W			
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W			
WattStopper	Slide	SD-603-W			

Brand	Model	Part #	Lamp Quantity		
			Best	OK	NR
Lutron	Skylark	CTCL-153P			
Lutron	Diva	DVCL-153PD			
Lutron	Diva	DVCL-153P v2	1-10		
Lutron	Diva	DVPDC-203			
Lutron	Diva	DV-600P	1-10		
Lutron	Diva	DV-603PG			
Lutron	DIVA	DVELV-300P	1-10		
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P			
Lutron	Maestro	MACL-153M v2	1-10		
Lutron	Maestro	MAELV-600			
Lutron	Maestro	MALV-600			
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120	1-10		
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600	1-10		
Lutron	Nova	NLV1000	1-10*		
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P	1-10*		
Lutron	Qoto	Q-600P			
Lutron	RADIO RA	RRD-6NA	1-10		
Lutron	Skylark	S-600P			
Lutron	Skylark	SELV-300P			
Lutron	Skylark	SLV-600P	1-10		
Lutron	Toggle	TG-600P			
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker, good dimming range. Possible minor pop-on.
OK	A minor, low % flicker which is hard to find, some limit of dim-range, relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Notes
Lamp load is limited to 25% of dimmer's incandescent rating unless higher value approved by dimmer manufacturer.
* - Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.
Latest Update 01/15/2013





Philips LED Lamps
17W/A21

Applicable Part Numbers
418590, 418400, 422220

Brand	Model	Part #	Lamp Quantity		
			Best	OK	NR
Cooper	REACT	RI061-VW-K2			
Leviton	Decora	6161			
Leviton	SureSlide	6613	1-8		
Leviton	SureSlide	6615P		1-8	
Leviton	SureSlide	6631			
Leviton	SureSlide	6633P			
Leviton	SureSlide	6674		1-8	
Leviton	Trimatron	6681	1-6		>6
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ			
Leviton	IllumaTech	IPI06	1-8		
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Lightolier	Vega	V600VAU	1-5		
Lightolier	Vega	V1000VAU			
Lightolier	Sunrise	ZP600VA	1-8		
Lightolier	Sunrise	ZP600			
Lightolier	Vega	V600			
Lightolier	Onset	OS600			
Lightolier	Onset	OS600VA	1-8		
Lightolier	Onset	OS1000VA			
Lightolier	Astral Slider	A600			
Lightolier	Astral Slider	AP600			
Lightolier	MultiSet	MHP600VA	1-8		
Lightolier	Momentum	MP2000VAI			
WattStopper	Micro Decorator	DCD267-W	1-8		
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W			
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W			
WattStopper	Slide	SD-603-W			

Brand	Model	Part #	Lamp Quantity		
			Best	OK	NR
Lutron	Skylark	CTCL-153P		1-8	
Lutron	Diva	DVCL-153PD	1-4		
Lutron	Diva	DVCL-153P v2	1-8		
Lutron	Diva	DVPDC-203			X
Lutron	Diva	DV-600P	1-8		
Lutron	Diva	DV-603PG		1-8	
Lutron	DIVA	DVELV-300P	1-8		
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P		1-8	
Lutron	Maestro	MACL-153M v2	1-8		
Lutron	Maestro	MAELV-600			
Lutron	Maestro	MALV-600			
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120	1-8		
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600	1-8		
Lutron	Nova	NLV1000	1-14		
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P	1-11*		
Lutron	Qoto	Q-600P			
Lutron	RADIO RA	RRD-6NA	1-8		
Lutron	Skylark	S-600P	1-8		
Lutron	Skylark	SELV-300P	1-8		
Lutron	Skylark	SLV-600P		1-4	
Lutron	Toggler	TG-600P		1-4	
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker, good dimming range. Possible minor pop-on.
OK	A minor, low % flicker which is hard to find, some limit of dim-range, relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity fo lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Notes
Lamp load is limited to 25% of dimmer's incandescent rating unless higher value approved by dimmer manufacturer.
* - Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.
Latest Update 01/15/2013





Philips LED Lamps
17W/PAR38

Applicable Part Numbers
410175, 410183, 410191, 414433, 414516, 414532, 414607, 414615

Brand	Model	Part #	Lamp Quantity		
			Best	OK	NR
Cooper	REACT	RI061-VW-K2			
Leviton	Decora	6161	1-7		
Leviton	SureSlide	6613	1-6		>6
Leviton	SureSlide	6615P		1-4	>4
Leviton	SureSlide	6631	1-8		
Leviton	SureSlide	6633P			
Leviton	SureSlide	6674	1-8		
Leviton	Trimatron	6681	1-2		>2
Leviton	Trimatron	6683	1-2		>2
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ	1-5		
Leviton	IllumaTech	IPI06			X
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			X
Lightolier	Vega	V600VAU	1-8		
Lightolier	Vega	V1000VAU			
Lightolier	Sunrise	ZP600VA		1-8	
Lightolier	Sunrise	ZP600			X
Lightolier	Vega	V600		1-5	>5
Lightolier	Onset	OS600			X
Lightolier	Onset	OS600VA		1-8	
Lightolier	Onset	OS1000VA		1-8	
Lightolier	Astral Slider	A600		1-5	>5
Lightolier	Astral Slider	AP600		1-4	>4
Lightolier	MultiSet	MHP600VA	1-4	5-8	
Lightolier	Momentum	MP2000VAI	1-15*		
WattStopper	Micro Decorator	DCD267-W	1-8		
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W	1-6	7-8	
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W			
WattStopper	Slide	SD-603-W	1-8		

Brand	Model	Part #	Lamp Quantity		
			Best	OK	NR
Lutron	Skylark	CTCL-153P			
Lutron	Diva	DVCL-153PD			X
Lutron	Diva	DVCL-153P v2	1-8		
Lutron	Diva	DVPDC-203			X
Lutron	Diva	DV-600P		1-8	
Lutron	Diva	DV-603PG	1-7		>7
Lutron	DIVA	DVELV-300P		1-4	>4
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P		1-8	
Lutron	Maestro	MAELV-600	1-8		
Lutron	Maestro	MAELV-600	1-8		
Lutron	Maestro	MALV-600			X
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120			X
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600	1-8		
Lutron	Nova	NLV1000	1-12*		
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P		1-4	>4
Lutron	Qoto	Q-600P		1-8	
Lutron	RADIO RA	RRD-6NA	1-8		
Lutron	Skylark	S-600P	1-7		>7
Lutron	Skylark	SELV-300P		1-4	>4
Lutron	Skylark	SLV-600P		1-8	
Lutron	Toggler	TG-600P		1-8	
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker, good dimming range. Possible minor pop-on.
OK	A minor, low % flicker which is hard to find, some limit of dim-range, relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Notes
Lamp load is limited to 25% of dimmer's incandescent rating unless higher value approved by dimmer manufacturer.
* - Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.
Latest Update 01/15/2013





**Philips LED Lamps
18W/PAR38**

Applicable Part Numbers
418525, 418533

Brand	Model	Part #	Lamp Quantity		
			Best	OK	NR
Cooper	REACT	RI061-VW-K2			
Leviton	Decora	6161			
Leviton	SureSlide	6613	1-8		
Leviton	SureSlide	6615P	1-8		
Leviton	SureSlide	6631			
Leviton	SureSlide	6633P			
Leviton	SureSlide	6674	1-8		
Leviton	Trimatron	6681	1-8		
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ			
Leviton	IllumaTech	IPI06	1-8		
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Lightolier	Vega	V600VAU	1-8		
Lightolier	Vega	V1000VAU			
Lightolier	Sunrise	ZP600VA	1-8		
Lightolier	Sunrise	ZP600			
Lightolier	Vega	V600			
Lightolier	Onset	OS600			
Lightolier	Onset	OS600VA	1-8		
Lightolier	Onset	OS1000VA			
Lightolier	Astral Slider	A600			
Lightolier	Astral Slider	AP600			
Lightolier	MultiSet	MHP600VA	1-8		
Lightolier	Momentum	MP2000VAI	1-11*		
WattStopper	Micro Decorator	DCD267-W	1-8		
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W	1-6		>6
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W	1-8		
WattStopper	Slide	SD-603-W		1-8	>8

Brand	Model	Part #	Lamp Quantity		
			Best	OK	NR
Lutron	Skylark	CTCL-153P			
Lutron	Divi	DVCL-153PD			
Lutron	Divi	DVCL-153P v2	1-8		
Lutron	Divi	DVPDC-203			
Lutron	Divi	DV-600P	1-8		
Lutron	Divi	DV-603PG			
Lutron	DIVA	DVELV-300P	1-8		
Lutron	Divi	DVWCL-153PDH			
Lutron	Glyder	GL-600P			
Lutron	Maestro	MACL-153M v2	1-8		
Lutron	Maestro	MAELV-600			
Lutron	Maestro	MALV-600			
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120	1-8		
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600	1-8		
Lutron	Nova	NLV1000	1-9*		
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P	1-10*		
Lutron	Qoto	Q-600P			
Lutron	RADIO RA	RRD-6NA	1-8		
Lutron	Skylark	S-600P			
Lutron	Skylark	SELV-300P			
Lutron	Skylark	SLV-600P	1-8		
Lutron	Toggler	TG-600P			
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker, good dimming range. Possible minor pop-on.
OK	A minor, low % flicker which is hard to find, some limit of dim-range, relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity fo lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Notes
Lamp load is limited to 25% of dimmer's incandescent rating unless higher value approved by dimmer manufacturer.
* - Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.
Latest Update 01/15/2013





Philips LED Lamps
19.5W/PAR38 (AirFlux)

Applicable Part Numbers
420513, 420521, 420885, 420893, 425405, 425413, 425421, 425439, 425447

Brand	Model	Part #	Lamp Quantity		
			Best	OK	NR
Cooper	REACT	RI061-VW-K2			X
Leviton	Decora	6161			
Leviton	SureSlide	6613	1-7		
Leviton	SureSlide	6615P		1-7	
Leviton	SureSlide	6631			
Leviton	SureSlide	6633P			
Leviton	SureSlide	6674		1-7	
Leviton	Trimatron	6681		1-7	
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ			
Leviton	IllumaTech	IPI06	1-2	3-7	
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Lightolier	Vega	V600VAU	1-7		
Lightolier	Vega	V1000VAU			
Lightolier	Sunrise	ZP600VA	1-7		
Lightolier	Sunrise	ZP600			
Lightolier	Vega	V600			
Lightolier	Onset	OS600			
Lightolier	Onset	OS600VA	1-7		
Lightolier	Onset	OS1000VA			
Lightolier	Astral Slider	A600			
Lightolier	Astral Slider	AP600			
Lightolier	MultiSet	MHP600VA	1-7		
Lightolier	Momentum	MP2000VAI			
WattStopper	Micro Decorator	DCD267-W	1-7		
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W	1-7		
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W	1-7		
WattStopper	Slide	SD-603-W	1-7		

Brand	Model	Part #	Lamp Quantity		
			Best	OK	NR
Lutron	Skylark	CTCL-153P			
Lutron	Divi	DVCL-153PD		1-7	
Lutron	Divi	DVCL-153P v2	1-7		
Lutron	Divi	DVPDC-203			
Lutron	Divi	DV-600P	1-7		
Lutron	Divi	DV-603PG			
Lutron	DIVA	DVELV-300P	1-7		
Lutron	Divi	DVWCL-153PDH			
Lutron	Glyder	GL-600P			
Lutron	Maestro	MACL-153M v2	1-7		
Lutron	Maestro	MAELV-600			
Lutron	Maestro	MALV-600			
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120	1-7		
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600	1-7		
Lutron	Nova	NLV1000	1-12		
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P	1-7*		
Lutron	Qoto	Q-600P			
Lutron	RADIO RA	RRD-6NA	1-7		
Lutron	Skylark	S-600P			
Lutron	Skylark	SELV-300P			
Lutron	Skylark	SLV-600P	1-7		
Lutron	Toggler	TG-600P			
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker, good dimming range. Possible minor pop-on.
OK	A minor, low % flicker which is hard to find, some limit of dim-range, relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Notes
Lamp load is limited to 25% of dimmer's incandescent rating unless higher value approved by dimmer manufacturer.
* - Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.
Latest Update 01/15/2013





Philips LED Lamps
22W/A21

Applicable Part Numbers
423525, 424432

Brand	Model	Part #	Lamp Quantity		
			Best	OK	NR
Cooper	REACT	RI061-VW-K2			x
Leviton	Decora	6161			
Leviton	SureSlide	6613			x
Leviton	SureSlide	6615P			x
Leviton	SureSlide	6631			
Leviton	SureSlide	6633P			
Leviton	SureSlide	6674			x
Leviton	Trimatron	6681			x
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ			
Leviton	IllumaTech	IPI06	1-6		
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Lightolier	Vega	V600VAU			x
Lightolier	Vega	V1000VAU			
Lightolier	Sunrise	ZP600VA		1-6	
Lightolier	Sunrise	ZP600			
Lightolier	Vega	V600			
Lightolier	Onset	OS600			
Lightolier	Onset	OS600VA	1-6		
Lightolier	Onset	OS1000VA			
Lightolier	Astral Slider	A600			
Lightolier	Astral Slider	AP600			
Lightolier	MultiSet	MHP600VA	1-6		
Lightolier	Momentum	MP2000VAI			
WattStopper	Micro Decorator	DCD267-W	1-6		
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W			
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W			
WattStopper	Slide	SD-603-W			

Brand	Model	Part #	Lamp Quantity		
			Best	OK	NR
Lutron	Skylark	CTCL-153P			
Lutron	Diva	DVCL-153PD			x
Lutron	Diva	DVCL-153P v2			x
Lutron	Diva	DVPDC-203			
Lutron	Diva	DV-600P			x
Lutron	Diva	DV-603PG			
Lutron	DIVA	DVELV-300P			x
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P			
Lutron	Maestro	MACL-153M v2	1-6		
Lutron	Maestro	MAELV-600	1-6		
Lutron	Maestro	MALV-600			
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120	1-6		
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600		1-6	
Lutron	Nova	NLV1000		1-10	
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P	1-8*		
Lutron	Qoto	Q-600P			x
Lutron	RADIO RA	RRD-6NA	1-6		
Lutron	Skylark	S-600P			
Lutron	Skylark	SELV-300P		1-6	
Lutron	Skylark	SLV-600P		1-6	
Lutron	Toggler	TG-600P			
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker, good dimming range. Possible minor pop-on.
OK	A minor, low % flicker which is hard to find, some limit of dim-range, relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity fo lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Notes
Lamp load is limited to 25% of dimmer's incandescent rating unless higher value approved by dimmer manufacturer.
* - Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.
Latest Update 01/15/2013

