



# T8 Plus

F32T8 TL765 ALTO Plus

Philips PLUS T8 lamps are energy-efficient lighting solutions and offer long life.

## Product data

### • General Characteristics

Base	Medium Bi-Pin [Medium Bi-Pin Fluorescent]
Base Information	Green Base
Bulb	T8
Energy Saving	Energy Saving
Rated Avg Life [12-Hr Prog St]	44000 hr
Rated Avg Life [12-Hr Inst St]	36000 hr
Rated Avg Life [3-Hr Prog St]	38000 hr
Rated Avg Life [3-Hr Inst St]	30000 hr

### • Light Technical Characteristics

Color Rendering Index	82 Ra8
Color Designation	TL765
Color Temperature	6500 K
Initial lumen	2750 Lm
Design Mean Lumens	2610 Lm

### • Electrical Characteristics

Watts	32 W
-------	------

### • Environmental Characteristics

Mercury (Hg) Content	1.7 mg
Picogram per Lumen Hour	22 p/LuHr

### • Product Dimensions

Nominal Length [inch]	48
-----------------------	----

### • Product Data

Product number	423061
Full product name	F32T8 TL765 ALTO Plus
Short product name	F32T8/TL765 PLUS/ALTO 30PK
Pieces per Sku	1
eop_pck_cfg	30
Skus/Case	30
Bar code on pack	46677423063
Bar code on case	50046677423068
Logistics code(s)	927852076501
eop_net_weight_pp	0.001 kg


# PHILIPS

sense and simplicity

Dimensional drawing



G13, T8



G13



G13, T8



© 2012 Koninklijke Philips Electronics N.V.  
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

[www.philips.com/lighting](http://www.philips.com/lighting)

2012, September 11  
data subject to change