



T8 Plus

F32T8/TL835 ALTO Plus

Philips PLUS T8 lamps are energy-efficient lighting solutions and offer long life.

Product data

• General Characteristics

Base	Medium Bi-Pin [Medium Bi-Pin Fluorescent]
Base Information	Green Base
Bulb	T8
Energy Saving	Energy Saving
Rated Avg Life [12-Hr Prog St]	44000 hr
Rated Avg Life [12-Hr Inst St]	36000 hr
Rated Avg Life [3-Hr Prog St]	38000 hr
Rated Avg Life [3-Hr Inst St]	30000 hr

• Light Technical Characteristics

Color Code	TL835 [CCT of 3500K]
Color Rendering Index	85 Ra8
Color Designation	TL835
Color Temperature	3500 K
Initial lumen	2950 Lm
Design Mean Lumens	2800 Lm

• Electrical Characteristics

Watts	32 W
-------	------

• Environmental Characteristics

Mercury (Hg) Content	1.7 mg
Picogram per Lumen Hour	20 p/LuHr

• Product Dimensions

Nominal Length [inch]	48
-----------------------	----

• Footnotes

Footnotes Fluorescent/CFL	920 [Circle E- The encircled E means this bulb meets Federal minimum efficiency standards.]
---------------------------	---


• Product Data

Product number	281675
Full product name	F32T8/TL835 ALTO Plus
Short product name	F32T8/TL835 PLUS ALTO 30PK
Pieces per Sku	1
eop_pck_cfg	30
Skus/Case	30
Bar code on pack	46677281670
Bar code on case	50046677281675
Logistics code(s)	927852083503
eop_net_weight_pp	0.001 kg


PHILIPS

sense and simplicity


Dimensional drawing



F32T8/TL835 ALTO Plus/TG



G13



F32T8/TL835 ALTO Plus/TG



© 2013 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2013, January 12
data subject to change