



# Advantage T8

F32T8 ADV830 ALTO

Philips Advantage T8 lamps are an energy-efficient solution and offer high lumen output.

## Product data

### • General Characteristics

Base	Medium Bi-Pin [Medium Bi-Pin Fluorescent]
Base Information	Green Base
Bulb	T8
Energy Saving	Energy Saving
Rated Avg Life [12-Hr Prog St]	36000 hr
Rated Avg Life [12-Hr Inst St]	30000 hr
Rated Avg Life [3-Hr Prog St]	30000 hr
Rated Avg Life [3-Hr Inst St]	24000 hr

### • Light Technical Characteristics

Color Code	Advantage 830 [CCT of 3000K]
Color Rendering Index	85 Ra8
Color Designation	Advantage 830
Color Temperature	3000 K
Initial lumen	3100 Lm
Design Mean Lumens	3000 Lm

### • Electrical Characteristics

Watts	32 W
-------	------

### • Environmental Characteristics

Mercury (Hg) Content	1.7 mg
Picogram per Lumen Hour	24 p/LuHr

### • Product Dimensions

Nominal Length [inch]	48
-----------------------	----

### • Footnotes

Footnotes Fluorescent/CFL	920 [Circle E- The encircled E means this bulb meets Federal minimum efficiency standards.]
---------------------------	---

### • Product Data

Product number	280800
Full product name	F32T8 ADV830 ALTO
Short product name	F32T8/ADV830 ALTO 30PK
Pieces per Sku	1
eop_pck_cfg	30
Skus/Case	30
Bar code on pack	46677280802
Bar code on case	50046677280807
Logistics code(s)	927869783102
eop_net_weight_pp	0.001 kg


# PHILIPS

sense and simplicity

Dimensional drawing



G13, T8



G13



G13, T8



© 2012 Koninklijke Philips Electronics N.V.  
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

[www.philips.com/lighting](http://www.philips.com/lighting)

2012, August 4  
data subject to change