



High CRI T12

F96T12 C50 Supreme ALTO

Philips T12 High CRI Lamps are energy-efficient lighting solutions and provide excellent color consistency over the life of the lamp.

Product data

• General Characteristics

Base	Single Pin [Single Pin Fluorescent]
Base Information	Green Base
Bulb	T12
Rated Avg. Life [3 hr Start]	12000 hr
Energy Saving	Energy Saving

• Light Technical Characteristics

Color Rendering Index	90 Ra8
Color Designation	C50 Supreme
Color Temperature	5000 K
Initial lumen	5000 Lm
Design Mean Lumens	4250 Lm

• Electrical Characteristics

Watts	75 W
-------	------

• Environmental Characteristics

Mercury (Hg) Content	6.8 mg
----------------------	--------

• Product Dimensions

Nominal Length [inch]	96
-----------------------	----

• Product Data


Product number	423871
Full product name	F96T12 C50 Supreme ALTO
Short product name	F96T12/C50Supreme/ALTO 15pk
Pieces per Sku	1
eop_pck_cfg	15
Skus/Case	15
Bar code on pack	46677423872
Bar code on case	50046677423877
Logistics code(s)	927895000211
eop_net_weight_pp	0.001 kg

Dimensional drawing

Dimensional drawing

FA8, T12

Product	C (Norm)	D (Max)
F96T12 C50 Supreme ALTO®	-	-



© 2012 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2012, August 4
data subject to change