



A-Shape LED

17A21/END/2700 DIM 6/1

Philips A-shape Dimmable LED lamps are the smart LED alternative to standard incandescents. The unique lamp design provides omi-directional light with excellent dimming performance.

Product data

• General Characteristics

Cap-Base	E26
Bulb	A21
Rated Avg. Life (Hours)	25000 hr

• Light Technical Characteristics

Color Code	WW
Color Designation	Warm White
Correlated Color Temperature	2700 K
CRI	80
Color Temp. (Kelvin)	2700 K [CCT 2700K]
Rated Luminous Flux	1100 Lm

• Electrical Characteristics

Wattage	17 W
Wattage Technical	17.0 W
Voltage	120 V

Power Factor	0.71 -
Lamp Current mA	195 mA
Dimmable	Yes

• Product Dimensions

Overall Length C [inch]	5.039 (max) in
-------------------------	----------------

• Product Data

Product number	418590
Full product name	17A21/END/2700 DIM 6/1
Short product name	17A21/END/2700-1100 DIM 6/1
Pieces per Sku	1
eop_pck_cfg	6
Skus/Case	6
Bar code on pack	46677418595
Bar code on case	50046677418590
Logistics code(s)	929000201804
eop_net_weight_pp	0.224 kg



PHILIPS

sense and simplicity