



# BR LED with AirFlux Technology

14BR40/END/F90 2700-800 DIM SM 6/1

Philips BR Dimmable LED Lamps with AirFlux technology provide a soft, diffused level of light and smooth dimming to reduce glare. The sleek, lightweight design is ideal for downlighting.

## Product data

### • General Characteristics

Cap-Base	E26
Bulb	BR40
Bulb Finish	White
Rated Avg. Life (Hours)	25000 hr

### • Light Technical Characteristics

Color Code	WW
Color Designation	Warm White
Correlated Color Temperature	2700 K
Approximate Lumens	800 Lm
CRI	80
Color Temp. (Kelvin)	2700 K [CCT 2700K]

### • Electrical Characteristics

Wattage	14.5 W
Wattage Technical	14.5 W
Voltage	120 V
Power Factor	0.7 -

Lamp Current mA	178 mA
Dimmable	Yes
Starting Time	0.5 (max) s

### • Product Dimensions

Diameter D	124.8 mm
Overall Length C	164.2 mm

### • Product Data

Product number	420562
Full product name	14BR40/END/F90 2700-800 DIM SM 6/1
Short product name	14BR40/END/F90 2700 DIM AF 6/1
Pieces per Sku	1
eop_pck_cfg	6
Skus/Case	6
Bar code on pack	46677420567
Bar code on case	50046677420562
Logistics code(s)	929000219904
eop_net_weight_pp	0.357 kg



# PHILIPS

sense and simplicity