

Philips Energy Saver
GU24 Twister Compact
Fluorescent Lamp

*Ideal for table and floor
lamps, ceiling fans and
reading lamps*

Energy Saver



Energy saving GU24 twisters

Philips Energy Saver GU24 Twister Compact Fluorescent Lamps feature a twist and lock connection with 2 pins for energy efficient replacement.

Easy retrofit for GU24 fixtures or luminaires

- Self ballasted
- Simple twist and lock design to allow quick and easy replacement
- Instant-on
- Compact size fits most GU24 fixtures
- ENERGY STAR® qualified

Long life

- Lasts 9 years*

Energy saving

- Saves up to \$77 over the life of the lamp when you replace a 100W A19 incandescent lamp with a 23W Energy Saver Twister GU24**

* Based on an average daily usage of 3–4 hours per day, 7 days per week.

** Based on wattage saved (77W) × replacement lamp rated average life (10,000 hours) divided by 1000 × kWh rate (.10) = \$77 saved.

PHILIPS

sense and simplicity

Philips Energy Saver GU24 Twister Compact Fluorescent Lamp

Ordering, Electrical and Technical Data (Subject to change without notice)

Product Number	Description	Watts	Volts	Approx. Incand. Equiv.	Base	Color Temp. (Kelvin)	CRI	Approx. Initial Lumens ¹	MOL (In.)	Diam. (In.)	Rated Avg. Life (Hrs.) ²	Min. Starting Temp. ³	Max. Starting Temp. ³
22285-1	EL/mdT 13W GU24	13	120	60A19	GU24	2700	82	900	3 $\frac{3}{8}$	1 $\frac{1}{2}$	10,000	-20°F/-29°C	185°F/85°C
22286-9	EL/mdT 18W GU24	18	120	75A19	GU24	2700	82	1200	3 $\frac{3}{8}$	2 $\frac{1}{2}$	10,000	-20°F/-29°C	185°F/85°C
22287-7	EL/mdT 23W GU24	23	120	100A19	GU24	2700	82	1600	4 $\frac{1}{8}$	2 $\frac{3}{4}$	10,000	-20°F/-29°C	185°F/85°C

Shipping Data

Product Number	SKU UPC (0-46677)	Outer Bar Code (5-00-46677)	Case Qty.	Case Weight (lbs.)	Case Cube (cu. ft.)	Pallet Qty.	SKUs Per Layer	Layers High	SKU Dimensions (W x D x H) (In.)	Case Dimensions (W x D x H) (In.)	Pallet Dimensions (W x D x H) (In.)
22285-1	22285-7	22285-2	6	1.9	0.084	2832	354	8	2.1 x 2.1 x 4.2	4.5 x 6.6 x 4.9	38.1 x 46.4 x 39.9
22286-9	22286-4	22286-9	6	2.5	0.133	1872	234	8	2.5 x 2.5 x 4.5	5.5 x 8.1 x 5.1	38.5 x 46.1 x 41.0
22287-7	22287-1	22287-6	6	2.8	0.159	1428	204	7	2.7 x 2.7 x 4.9	5.8 x 8.5 x 5.6	37.0 x 46.0 x 39.4

1) Approximate initial lumens. The lamp lumen output is based upon lamp performance after 100 hours of operating life under standard laboratory conditions.

2) Average life under specified test conditions with lamps turned off and restarted no more frequently than once every 3 operating hours. Use in recessed cans or enclosed indoor fixtures could result in reduced lamp life.

3) The minimum and maximum starting temperature is the temperature at which the lamp will reliably start.

■ ENERGY STAR® Bulb: As an ENERGY STAR® Partner, Philips has determined that this product meets the ENERGY STAR® guidelines for energy efficiency.

WARNINGS AND CAUTIONS: Do not use with dimmers. Some electronic timer and photo sensor switches contain dimming circuitry, so before using such a switch, check with its manufacturer to ensure compatibility with electronic CFL bulbs. Do not use with emergency exit fixtures or lights. Outdoor use requires a weather-protected fixture. Turn off power before changing bulb. This device complies with Part 18 of the FCC Rules. Reliable operating temperature range -20°F/-29°C to 185°F/85°C.

Note: This product may cause interference with radios, televisions, telephones, or remote controls. If interference occurs, move this product away from device or plug into another outlet.



Bulb Type	Table/Floor Lamp	Outdoor Postlight	Wall Sconce	Surface Mount	Reading Lamp	Recessed Fixture	Outdoor Security	Open Hanging	Vanity Strip	Ceiling Fan	Rough Service
Genie	•	•	•	•	•			•			
Twister	•	•	•	•	•			•			
GU24	•	•	•	•	•		•	•		•	
Universal	•	•	•	•	•	•		•			
Reflector Flood						•					
Fast Run-Up						•	•				
Candle		•	•					•		•	
Vanity & Decor Globe								•	•	•	
A-Shape	•	•	•		•			•		•	
Outdoor		•					•				
Tuffguard											•



© 2010 Philips Lighting Company. All rights reserved.
Printed in USA 5/10

P-5957-A

www.philips.com

Philips Lighting Company
200 Franklin Square Drive
Somerset, NJ 08873
1-800-555-0050

A Division of Philips Electronics North America Corporation

Philips Lighting
281 Hillmount Road
Markham, Ontario
Canada L6C 2S3
1-800-555-0050

A Division of Philips Electronics Ltd.