

Philips Family of Specialty Incandescents provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications. Rough Service incandescent lamps have an exceptionally strong filament for which a special filament wire is used, which makes these lamps extremely suitable for places where shocks, bumps and vibrations frequently occur. The clear version, with its completely visible filament, is a brilliant light source, whereas the inside-frosted lamp is used wherever well diffused light is required.

## Product data

### • General Characteristics

Base	Medium [Single Contact Medium Screw]
Base Information	Aluminum [Aluminum Base]
Bulb	A19
Bulb Finish	Frosted
Filament Shape	RC-9 [Reinforced Construction C-9]
Operating Position	Universal [Any or Universal (U)]
Main Application	Rough Service
Atmosphere	Gas

### • Light Technical Characteristics

Initial lumen	235 Lm
---------------	--------

### • Electrical Characteristics

Watts	25 W
Voltage	120-130 V

### • Product Dimensions

Max Overall Length (MOL) - C	3.938 (max) in
Diameter D	2.375 in

### • Product Data

Product number	373860
Full product name	25W Med 120-130V A19 FR 2WR
Short product name	25W Med 120-130V A19 FR 2WR
Pieces per Sku	1
eop_pck_cfg	120
Skus/Case	120
Bar code on pack	46677373863
Bar code on case	50046677373868
Logistics code(s)	920585035502
eop_net_weight_pp	0.001 kg