

50W Med 250V A19 FR 2WR

The Philips Family of Standard Frost and Clear bulbs are good for everyday use. Clear bulbs provide sparkle, especially in fixtures that are made of chrome, have mirrored surfaces, multiple sockets or have cut glass parts. If glare is a problem, use a dimmer or a lower wattage bulb to reduce brightness. Clear bulbs are also used in fixtures with reflectors. Frost bulbs provide soft light with reduced glare.

Product data

• General Characteristics

Base	Medium [Single Contact Medium Screw]
Base Information	Aluminum [Aluminum Base]
Bulb	A19
Bulb Finish	Frosted
Filament Shape	RC-9 [Reinforced Construction C-9]
Operating Position	Universal [Any or Universal (U)]
Main Application	General Lighting
Atmosphere	Gas

• Light Technical Characteristics

Initial lumen	355 Lm
---------------	--------

• Electrical Characteristics

Watts	50 W
Voltage	250 V

• Product Dimensions

Max Overall Length (MOL) - C	3.938 (max) in
Diameter D	2.375 in

• Product Data

Product number	245696
Full product name	50W Med 250V A19 FR 2WR
Short product name	50W Med 250V A19 FR 2WR
Pieces per Sku	1
eop_pck_cfg	120
Skus/Case	120
Bar code on pack	46677245696
Bar code on case	50046677245691
Logistics code(s)	920585546203
eop_net_weight_pp	0.001 kg