



Frost / Clear

60W 130V A19 CL 2WR

The Philips Family of Standard Frost and Clear bulbs are good for everyday use. Clear bulbs provide sparkle, especially in fixtures that are made of chrome, have mirrored surfaces, multiple sockets or have cut glass parts. If glare is a problem, use a dimmer or a lower wattage bulb to reduce brightness. Clear bulbs are also used in fixtures with reflectors. Frost bulbs provide soft light with reduced glare.

Product data

• General Characteristics

Base	Medium [Single Contact Medium Screw]
Base Information	Aluminum [Aluminum Base]
Bulb	A19
Bulb Finish	Clear
Filament Shape	CC6 [Straight]
Operating Position	Universal [Any or Universal (U)]
Main Application	General Lighting
Atmosphere	Gas
Rated Avg. Life @ 120v	1000 hr
Estimated Energy Cost/YR	7.23 \$
Life with 3h/day use [years]	0.5 an

• Light Technical Characteristics

Color Temperature	2820 K
Initial lumen	965 Lm
Initial Lumens @ 120V	730 Lm

• Electrical Characteristics

Watts	60 W
Voltage	130 V

• Product Dimensions

Light Center Length L	3.125 in
Max Overall Length (MOL) - C	4.438 (max) in
Diameter D	2.375 in

• Footnotes


Footnotes Incandescent	909 [Pursuant to California law, these incandescent lamps CANNOT be used or offered for sale in the state of California.(909)]
------------------------	--

• Product Data

Product number	375220
Full product name	60W 130V A19 CL 2WR
Short product name	60W 130V A19 CL 2WR
Pieces per Sku	1
eop_pck_cfg	48
Skus/Case	48
Bar code on pack	46677375225
Bar code on case	50046677375220
Logistics code(s)	920621036102
eop_net_weight_pp	0.001 kg

Dimensional drawing

Dimensional drawing



A19



E26

E26, A19

Product	C (Max)	D (Norm)
Std 60W E26 130V A19 CL	4.438	2.375



© 2012 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2012, July 31
data subject to change