



Frost / Clear

75W Med 120V A19 FR 2WR

The Philips Family of Standard Frost and Clear bulbs are good for everyday use. Clear bulbs provide sparkle, especially in fixtures that are made of chrome, have mirrored surfaces, multiple sockets or have cut glass parts. If glare is a problem, use a dimmer or a lower wattage bulb to reduce brightness. Clear bulbs are also used in fixtures with reflectors. Frost bulbs provide soft light with reduced glare.

Product data

• General Characteristics

Base	Medium [Single Contact Medium Screw]
Base Information	Aluminum [Aluminum Base]
Bulb	A19
Bulb Finish	Frosted
Filament Shape	CC6 [Straight]
Operating Position	Universal [Any or Universal (U)]
Main Application	General Lighting
Atmosphere	Gas

• Light Technical Characteristics

Initial lumen	1100 Lm
---------------	---------

• Electrical Characteristics

Watts	75 W
Voltage	120 V

• Product Dimensions

Light Center Length L	2.980 in
--------------------------	----------

Max Overall Length (MOL) - C	4.134 (max) in
Diameter D	2.375 in

• Footnotes


Footnotes Incandescent	905 [Consider the compact fluorescent lamps for energy savings.]
Footnotes Incandescent	909 [Pursuant to California law, these incandescent lamps CANNOT be used or offered in the state of California. (909)]

• Product Data

Product number	374728
Pieces per Sku	1
eop_pck_cfg	48
Skus/Case	48
Bar code on pack	46677374723
Bar code on case	50046677374728
Logistics code(s)	920630136321
eop_net_weight_pp	0.001 kg

Dimensional drawing

Dimensional drawing



A19



E26

E26, A19

Product	C (Max)	D (Norm)
Std 75W E26 120V A19 FR	4.134	2.375



© 2012 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2012, July 31
data subject to change