

Philips Family of Specialty Incandescents provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications. Rough Service incandescent lamps have an exceptionally strong filament for which a special filament wire is used, which makes these lamps extremely suitable for places where shocks, bumps and vibrations frequently occur. The clear version, with its completely visible filament, is a brilliant light source, whereas the inside-frosted lamp is used wherever well diffused light is required.

Product data

• General Characteristics

Base	Medium [Single Contact Medium Screw]
Base Information	Brass [Brass Base]
Bulb	A21
Bulb Finish	Frosted
Filament Shape	RC-9 [Reinforced Construction C-9]
Operating Position	Universal [Any or Universal (U)]
Main Application	Rough Service
Atmosphere	Gas

• Light Technical Characteristics

Initial lumen	750 Lm
---------------	--------

• Electrical Characteristics

Watts	75 W
Voltage	120-130 V

• Product Dimensions

Max Overall Length (MOL) - C	5.313 (max) in
Diameter D	2.625 in

• Product Data

Product number	204701
Full product name	75W 120-130V A21 FR RS 1SL
Short product name	75W 120-130V A21 FR RS 1SL
Pieces per Sku	1
eop_pck_cfg	12
Skus/Case	12
Bar code on pack	46677104061
Bar code on case	50046677104066
Logistics code(s)	920636636305
eop_net_weight_pp	0.001 kg