



Hi Intensity

Hi Intensity 40W 120V S11 CL TP 1BC

Incandescent Hi Intensity light bulbs.

Product data

• General Characteristics

Base	Intermediate [Intermediate Screw]
Base Information	Aluminum [Aluminum Base]
Bulb	S11
Bulb Finish	Clear
Filament Shape	CC-2V [Straight V]
Operating Position	Universal [Any or Universal (U)]
Main Application	High Intensity
Atmosphere	Gas
Estimated Energy Cost/YR	4.82 \$
Life with 3h/day use [years]	0.5 an

• Light Technical Characteristics

Initial lumen	440 Lm
---------------	--------

• Electrical Characteristics

Watts	40 W
Voltage	120 V

• Product Dimensions

Max Overall Length (MOL) - C	2.25 (max) in
Diameter D	1.375 in

• Product Data

Product number	212167
Full product name	Hi Intensity 40W 120V S11 CL TP 1BC
Short product name	Hi Intensity 40W 120V S11 CL TP 1BC
Pieces per Sku	1
eop_pck_cfg	16
Skus/Case	16
Bar code on pack	46677100377
Bar code on case	60046677100379
Logistics code(s)	922743936303
eop_net_weight_pp	0.001 kg

PHILIPS

sense and simplicity