

PAR30L

75W Med 120V PAR30L WFL 40D CL 1CT



Philips Halogen PAR lamps will provide bright, white light across the product line and feature excellent beam qualities for accent or ambient lighting. Their optimized coil and burner design allows for clear, crisp lighting effects with excellent color rendering, making it easy to optimize the look and feel of your store and your merchandise.

Product data

• General Characteristics

Base	Medium [Single Contact Medium Screw]
Base Information	Brass [Brass Base]
Bulb	PAR30L [PAR 3.75 inch/95mm Long]
Bulb Material	Hard Glass
Bulb Finish	Clear
Reflector Finish	Aluminized
Filament Shape	CC-8 [Axial]
Operating Position	Universal [Any or Universal (U)]
Main Application	Indoor Reflector
Atmosphere	Gas
RatedAvgLife(See Family Notes)	3000 hr
Estimated Energy Cost/YR	9.03 \$
Life with 3h/day use [years]	2.7 an

• Light Technical Characteristics

Beam Description	Wide Flood
Beam Angle	40 D
Approx. MBCP	1650 cd
Color Rendering Index	100 Ra8
Color Temperature	2860 K

Initial lumen 975 Lm

• Electrical Characteristics

Watts	75 W
Voltage	120 V


• Product Dimensions

Max Overall Length (MOL) - C	4.5 (max) in
Diameter D	3.75 in


• Product Data

Product number	229443
Full product name	75W Med 120V PAR30L WFL 40D CL 1CT
Short product name	75W Med 120V PAR30L WFL 40D CL 1CT
Pieces per Sku	1
eop_pck_cfg	15
Skus/Case	15
Bar code on pack	46677229443
Bar code on case	50046677229448
Logistics code(s)	924757100607
eop_net_weight_pp	0.001 kg

Dimensional drawing



E26, PAR30L



E26, PAR30L



E26



© 2012 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2012, August 4
data subject to change