

# PAR30S

75W 120V PAR30S FL 1CT



Philips Halogen PAR lamps will provide bright, white light across the product line and feature excellent beam qualities for accent or ambient lighting. Their optimized coil and burner design allows for clear, crisp lighting effects with excellent color rendering, making it easy to optimize the look and feel of your store and your merchandise.

## Product data

### • General Characteristics

Base	Medium [Single Contact Medium Screw]
Base Information	Brass [Brass Base]
Bulb	PAR30S [PAR 3.75 inch/95mm Short]
Bulb Material	Hard Glass
Bulb Finish	Clear
Reflector Finish	Aluminized
Filament Shape	CC-8 [Axial]
Operating Position	Universal [Any or Universal (U)]
Main Application	Indoor Reflector
Atmosphere	Gas
RatedAvgLife(See Family Notes)	3500 hr

### • Light Technical Characteristics

Beam Description	Flood [Flood]
Beam Angle	30 D
Approx. MBCP	4100 cd
Color Rendering Index	100 Ra8
Color Temperature	2900 K
Initial lumen	1050 Lm

### • Electrical Characteristics

Watts	75 W
Voltage	120 V


### • Product Dimensions

Max Overall Length (MOL) - C	3.625 (max) in
Diameter D	3.75 in


### • Product Data

Product number	284885
Full product name	75W 120V PAR30S FL 1CT
Short product name	75W 120V PAR30S FL 1CT
Pieces per Sku	1
eop_pck_cfg	15
Skus/Case	15
Bar code on pack	46677284886
Bar code on case	50046677284881
Logistics code(s)	924757108103
eop_net_weight_pp	0.241 kg

Dimensional drawing



E26, PAR30S



E26, PAR30S



E26



© 2012 Koninklijke Philips Electronics N.V.  
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

[www.philips.com/lighting](http://www.philips.com/lighting)

2012, August 4  
data subject to change