

# D.C. Bayonet

100W DC Bay 120V T4 CL 1CT



Accent lighting with improved lumens and higher performanceHalogen DC Bayonett Capsule lamps provide bright,white light for decorative and accent lighting and general illumination. Offered in T4 bulb size with DC Bayonette base configurations. These lamps offer a rated average life ranging from 1000 to 2000 hours depending upon the product.\* \* Rated average life is the length of operation (in hours) at which point an average of 50% of the lamps will still be operational and 50% will not.

## Product data

### • General Characteristics

Base	Double Contact Bayonet
Base Information	Aluminum [Aluminum Base]
Bulb	T4
Bulb Material	Std-Q [Standard Quartz]
Bulb Finish	Clear
Filament Shape	CC-8 [Axial]
Operating Position	Universal [Any or Universal (U)]
Main Application	General Lighting
Atmosphere	Gas
RatedAvgLife(See Family Notes)	1000 hr

### • Light Technical Characteristics

Color Rendering Index	100 Ra8
Color Temperature	2700 K
Initial lumen	1900 Lm

### • Electrical Characteristics

Watts	100 W
-------	-------

Voltage	120 V
---------	-------

### • Product Dimensions

Light Center Length L	1.38 in
Max Overall Length (MOL) - C	2.75 (max) in
Diameter D	5 in


### • Product Data

Product number	442780
Full product name	100W DC Bay 120V T4 CL 1CT
Short product name	100W DC Bay 120V T4 CL 1CT
Pieces per Sku	1
eop_pck_cfg	12
Skus/Case	12
Bar code on pack	46677115074
Bar code on case	50046677115079
Logistics code(s)	924794736381
eop_net_weight_pp	0.009 kg


# PHILIPS

sense and simplicity

Dimensional drawing



BA15d, T-4



BA15d, T-4



© 2012 Koninklijke Philips Electronics N.V.  
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

[www.philips.com/lighting](http://www.philips.com/lighting)

2012, August 4  
data subject to change