



Standard Life PS

Std 500W Mog 120V PS35 CL 1CT

Standard Life Incandescent, vacuum or gas-filled lamp has a crystal clear bulb and a completely visible filament, so the brightness of the light is not 'softened.' It imparts a sparkling radiance to larger luminaires and wall brackets with textured or satin-etched glass and cut crystal. It is the appropriate lamp for large luminaires with clear glass bowls, mounted indoors or outdoors. It is recommended in all such cases where brilliance and sparkle are more important than the avoidance of glare. These lamps are also used for indirect lighting in closed luminaires.

Product data

• General Characteristics

Base	Mogul [Mogul]
Base Information	Brass [Brass Base]
Bulb	PS35
Bulb Finish	Clear
Filament Shape	C-9 [Pendant]
Operating Position	Universal [Any or Universal (U)]
Main Application	General Lighting
Atmosphere	Gas

• Light Technical Characteristics

Initial lumen	8900 Lm
---------------	---------

• Electrical Characteristics

Watts	500 W
Voltage	120 V

• Product Dimensions

Max Overall Length (MOL) - C	9.375 (max) in
------------------------------	----------------

• Product Data

Product number	144071
Full product name	Std 500W Mog 120V PS35 CL 1CT
Short product name	Std 500W Mog 120V PS35 CL 1CT
Pieces per Sku	1
eop_pck_cfg	24
Skus/Case	24
Bar code on pack	46677144074
Bar code on case	50046677144079
Logistics code(s)	925159836101
eop_net_weight_pp	0.001 kg

PHILIPS

sense and simplicity