

DuraMax Soft White



DuraMax 40W ES 120V A-19 WH 40W

Philips DuraMax® Long Life Light Bulbs reduce the hassle of replacing light bulbs every few months, since all DuraMax products last longer than standard incandescent light bulbs. A wide assortment of shapes, sizes and wattages ensure that there is a DuraMax product to meet most basic lighting needs.

Product data

• General Characteristics

Base	Medium [Single Contact Medium Screw]
Base Information	Aluminum [Aluminum Base]
Bulb	A19
Bulb Finish	Soft White
Filament Shape	CC6 [Straight]
Operating Position	Universal [Any or Universal (U)]
Main Application	Household
Atmosphere	Gas
Estimated Energy Cost/YR	4.82 \$
Life with 3h/day use [years]	1.4 an

• Light Technical Characteristics

Color Temperature	2650 (nom), 2690 (max) K
Initial lumen	450 Lm

• Electrical Characteristics

Watts	40 W
Voltage	120 V

• Product Dimensions

Light Center Length L	2.953 in
-----------------------	----------

Max Overall Length (MOL) - C	4.438 (max) in
Diameter D	2.375 in

• Footnotes


Footnotes Incandescent	909 [Pursuant to California law, these incandescent lamps CANNOT be used or offered for sale in the state of California.(909)]
------------------------	--

• Product Data

Product number	168690
Full product name	DuraMax 40W ES 120V A-19 WH 40W
Short product name	DuraMax 40W ES 120V A-19 WH 40W
Pieces per Sku	4
eop_pck_cfg	12
Skus/Case	12
Bar code on pack	46677168698
Bar code on case	50046677168693
Logistics code(s)	925181236321
eop_net_weight_pp	0.000 kg

Dimensional drawing

Dimensional drawing



A19



E26

E26, A19

Product	C (Max)	D (Norm)
Std 40W E26 120V A19 SW	4.438	2.375



© 2012 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2012, August 4
data subject to change