



# Rough / Vibration Service

300W Mog 120-130V PS35 FR 1CT

Philips Family of Specialty Incandescents provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications. Rough Service incandescent lamps have an exceptionally strong filament for which a special filament wire is used, which makes these lamps extremely suitable for places where shocks, bumps and vibrations frequently occur. The clear version, with its completely visible filament, is a brilliant light source, whereas the inside-frosted lamp is used wherever well diffused light is required.

## Product data

### • General Characteristics

Base	Mogul [Mogul]
Base Information	Aluminum [Aluminum Base]
Bulb	PS35
Bulb Finish	Frosted
Filament Shape	C-9 [Pendant]
Operating Position	Universal [Any or Universal (U)]
Main Application	General Lighting
Atmosphere	Gas

### • Light Technical Characteristics

Initial lumen	5700 Lm
---------------	---------

### • Electrical Characteristics

Watts	300 W
Voltage	120-130 V

### • Product Dimensions

Max Overall Length (MOL) - C	9.375 (max) in
------------------------------	----------------

### • Product Data

Product number	143164
Full product name	300W Mog 120-130V PS35 FR 1CT
Short product name	300W Mog 120-130V PS35 FR 1CT
Pieces per Sku	1
eop_pck_cfg	12
Skus/Case	12
Bar code on pack	46677143169
Bar code on case	50046677143164
Logistics code(s)	925268434302
eop_net_weight_pp	0.001 kg

# PHILIPS

sense and simplicity