



Extended Service

Ext Ser 300W Mog 120V PS35 FR 1CT

Philips Econ-o-watt® Extended Service Lamps can directly replace standard life incandescent lamps, offering instant energy savings for many applications.

Product data

• General Characteristics

Base	Mogul [Mogul]
Base Information	Brass [Brass Base]
Bulb	PS35
Bulb Finish	Frosted
Filament Shape	C-9 [Pendant]
Operating Position	Universal [Any or Universal (U)]
Main Application	Extended Service
Atmosphere	Gas

• Light Technical Characteristics

Initial lumen	5020 Lm
---------------	---------

• Electrical Characteristics

Watts	300 W
Voltage	120 V

• Product Dimensions

Max Overall Length (MOL) - C	9.375 (max) in
------------------------------	----------------

• Product Data

Product number	143099
Full product name	Ext Ser 300W Mog 120V PS35 FR 1CT
Short product name	ExtSer 300W Mog 120V PS35 FR 1CT
Pieces per Sku	1
eop_pck_cfg	24
Skus/Case	24
Bar code on pack	46677143091
Bar code on case	50046677143096
Logistics code(s)	925268836102
eop_net_weight_pp	0.001 kg

PHILIPS

sense and simplicity