



Rough / Vibration Service

300W Mog 120V PS35 CL 1CT

Philips Family of Specialty Incandescents provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications. Rough Service incandescent lamps have an exceptionally strong filament for which a special filament wire is used, which makes these lamps extremely suitable for places where shocks, bumps and vibrations frequently occur. The clear version, with its completely visible filament, is a brilliant light source, whereas the inside-frosted lamp is used wherever well diffused light is required.

Product data

• General Characteristics

| | |
|--------------------|----------------------------------|
| Base | Mogul [Mogul] |
| Base Information | Brass [Brass Base] |
| Bulb | PS35 |
| Bulb Finish | Clear |
| Filament Shape | C-9 [Pendant] |
| Operating Position | Universal [Any or Universal (U)] |
| Main Application | General Lighting |
| Atmosphere | Gas |

• Light Technical Characteristics

| | |
|---------------|---------|
| Initial lumen | 4600 Lm |
|---------------|---------|

• Electrical Characteristics

| | |
|---------|-------|
| Watts | 300 W |
| Voltage | 120 V |

• Product Dimensions

| | |
|------------------------------|----------------|
| Max Overall Length (MOL) - C | 9.375 (max) in |
|------------------------------|----------------|

• Product Data

| | |
|--------------------|---------------------------|
| Product number | 143149 |
| Full product name | 300W Mog 120V PS35 CL 1CT |
| Short product name | 300W Mog 120V PS35 CL 1CT |
| Pieces per Sku | 1 |
| eop_pck_cfg | 24 |
| Skus/Case | 24 |
| Bar code on pack | 46677143145 |
| Bar code on case | 50046677143140 |
| Logistics code(s) | 925268936102 |
| eop_net_weight_pp | 0.001 kg |

PHILIPS

sense and simplicity