

100W 120-130V A21 FR 2WR

Philips Family of Specialty Incandescents provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications. Rough Service incandescent lamps have an exceptionally strong filament for which a special filament wire is used, which makes these lamps extremely suitable for places where shocks, bumps and vibrations frequently occur. The clear version, with its completely visible filament, is a brilliant light source, whereas the inside-frosted lamp is used wherever well diffused light is required.

Product data

• General Characteristics

Base	Medium [Single Contact Medium Screw]
Base Information	Brass [Brass Base]
Bulb	A21
Bulb Finish	Frosted
Filament Shape	RC-9 [Reinforced Construction C-9]
Operating Position	Universal [Any or Universal (U)]
Main Application	Rough & Vibration Service
Atmosphere	Gas
Rated Avg. Life @ 120v	1700 hr

• Light Technical Characteristics

Initial lumen	1230 Lm
Initial Lumens @ 120V	945 Lm

• Electrical Characteristics

Watts	100 W
-------	-------

Voltage	120-130 V
---------	-----------

• Product Dimensions

Max Overall Length (MOL) - C	5.313 (max) in
Diameter D	2.625 in

• Product Data

Product number	275693
Full product name	100W 120-130V A21 FR 2WR
Short product name	100W 120-130V A21 FR 2WR
Pieces per Sku	1
eop_pck_cfg	60
Skus/Case	60
Bar code on pack	46677275693
Bar code on case	50046677275698
Logistics code(s)	925286135502
eop_net_weight_pp	0.001 kg