

150W 120-130V A21 FR RVBRS 2WR

Philips Family of Specialty Incandescents provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications. Rough Service incandescent lamps have an exceptionally strong filament for which a special filament wire is used, which makes these lamps extremely suitable for places where shocks, bumps and vibrations frequently occur. The clear version, with its completely visible filament, is a brilliant light source, whereas the inside-frosted lamp is used wherever well diffused light is required.

Product data

• General Characteristics

Base	Medium [Single Contact Medium Screw]
Base Information	Brass [Brass Base]
Bulb	A21
Bulb Finish	Frosted
Filament Shape	Reinforced Construction [Reinforced]
Operating Position	Universal [Any or Universal (U)]
Main Application	Rough & Vibration Service
Atmosphere	Gas
Rated Avg. Life @ 120v	1700 hr

• Light Technical Characteristics

Initial lumen	2205 Lm
Initial Lumens @ 120V	1915 Lm

• Electrical Characteristics

Watts	150 W
-------	-------

Voltage	120-130 V
---------	-----------

• Product Dimensions

Max Overall Length (MOL) - C	5.313 (max) in
Diameter D	2.625 in

• Product Data

Product number	275784
Full product name	150W 120-130V A21 FR RVBRS 2WR
Short product name	150W 120-130V A21 FR RVBRS 2WR
Pieces per Sku	1
eop_pck_cfg	60
Skus/Case	60
Bar code on pack	46677275785
Bar code on case	50046677275780
Logistics code(s)	925287435502
eop_net_weight_pp	0.001 kg