



# Advantage T8

F17T8 ADV835 ALTO

Philips Advantage T8 lamps are an energy-efficient solution and offer high lumen output.

## Product data

### • General Characteristics

Base	Medium Bi-Pin [Medium Bi-Pin Fluorescent]
Base Information	Green Base
Bulb	T8
Energy Saving	Energy Saving
Rated Avg Life [12-Hr Prog St]	36000 hr
Rated Avg Life [12-Hr Inst St]	30000 hr
Rated Avg Life [3-Hr Prog St]	30000 hr
Rated Avg Life [3-Hr Inst St]	24000 hr

### • Light Technical Characteristics

Color Code	Advantage 835 [CCT of 3500K]
Color Rendering Index	85 Ra8
Color Designation	Advantage 835
Color Temperature	3500 K
Initial lumen	1450 Lm
Design Mean Lumens	1405 Lm

### • Electrical Characteristics

Watts	17 W
-------	------

### • Environmental Characteristics

Mercury (Hg) Content	1.7 mg
Picogram per Lumen Hour	50 p/LuHr

### • Product Dimensions

Nominal Length [inch]	24
-----------------------	----

### • Product Data

Product number	204842
Full product name	F17T8 ADV835 ALTO
Short product name	F17T8/ADV835 ALTO 25PK
Pieces per Sku	1
eop_pck_cfg	25
Skus/Case	25
Bar code on pack	46677204846
Bar code on case	50046677204841
Logistics code(s)	927850083601
eop_net_weight_pp	0.001 kg


# PHILIPS

sense and simplicity

Dimensional drawing



G13, T8



G13



G13, T8



© 2012 Koninklijke Philips Electronics N.V.  
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

[www.philips.com/lighting](http://www.philips.com/lighting)

2012, August 4  
data subject to change