



Advantage T8

F17T8 ADV841 ALTO

Philips Advantage T8 lamps are an energy-efficient solution and offer high lumen output.

Product data

• General Characteristics

Base	Medium Bi-Pin [Medium Bi-Pin Fluorescent]
Base Information	Green Base
Bulb	T8
Energy Saving	Energy Saving
Rated Avg Life [12-Hr Prog St]	36000 hr
Rated Avg Life [12-Hr Inst St]	30000 hr
Rated Avg Life [3-Hr Prog St]	30000 hr
Rated Avg Life [3-Hr Inst St]	24000 hr

• Light Technical Characteristics

Color Code	Advantage 841 [CCT of 4100K]
Color Rendering Index	85 Ra8
Color Designation	Advantage 841
Color Temperature	4100 K
Initial lumen	1450 Lm
Design Mean Lumens	1405 Lm

• Electrical Characteristics

Watts	17 W
-------	------

• Environmental Characteristics

Mercury (Hg) Content	1.7 mg
Picogram per Lumen Hour	50 p/LuHr

• Product Dimensions

Nominal Length [inch]	24
-----------------------	----

• Product Data

Product number	204859
Full product name	F17T8 ADV841 ALTO
Short product name	F17T8/ADV841 ALTO 25PK
Pieces per Sku	1
eop_pck_cfg	25
Skus/Case	25
Bar code on pack	46677204853
Bar code on case	50046677204858
Logistics code(s)	927850084201
eop_net_weight_pp	0.001 kg


PHILIPS

sense and simplicity

Dimensional drawing



G13, T8



G13



G13, T8



© 2012 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2012, August 4
data subject to change