



Advantage T8

F25T8 ADV841 ALTO

Philips Advantage T8 lamps are an energy-efficient solution and offer high lumen output.

Product data

• General Characteristics

| | |
|--------------------------------|---|
| Base | Medium Bi-Pin [Medium Bi-Pin Fluorescent] |
| Base Information | Green Base |
| Bulb | T8 |
| Energy Saving | Energy Saving |
| Rated Avg Life [12-Hr Prog St] | 36000 hr |
| Rated Avg Life [12-Hr Inst St] | 30000 hr |
| Rated Avg Life [3-Hr Prog St] | 30000 hr |
| Rated Avg Life [3-Hr Inst St] | 24000 hr |

• Light Technical Characteristics

| | |
|-----------------------|------------------------------|
| Color Code | Advantage 841 [CCT of 4100K] |
| Color Rendering Index | 85 Ra8 |
| Color Designation | Advantage 841 |
| Color Temperature | 4100 K |
| Initial lumen | 2250 Lm |
| Design Mean Lumens | 2185 Lm |

• Electrical Characteristics

| | |
|-------|------|
| Watts | 25 W |
|-------|------|

• Environmental Characteristics

| | |
|-------------------------|-----------|
| Mercury (Hg) Content | 1.7 mg |
| Picogram per Lumen Hour | 32 p/LuHr |

• Product Dimensions

| | |
|-----------------------|----|
| Nominal Length [inch] | 36 |
|-----------------------|----|


• Product Data

| | |
|--------------------|------------------------|
| Product number | 204958 |
| Full product name | F25T8 ADV841 ALTO |
| Short product name | F25T8/ADV841 ALTO 25PK |
| Pieces per Sku | 1 |
| eop_pck_cfg | 25 |
| Skus/Case | 25 |
| Bar code on pack | 46677204952 |
| Bar code on case | 50046677204957 |
| Logistics code(s) | 927851084201 |
| eop_net_weight_pp | 0.001 kg |


PHILIPS

sense and simplicity


Dimensional drawing



G13, T8



G13



G13, T8



© 2012 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2012, August 4
data subject to change